



Ecofit Ledtubes T8

16W (36W) G13 Cool White Non-dimmable Linear tube

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data

General Information		Power Consumption	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	16 W
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Rated Lifetime (Hours)	15,000 hour(s)	Power Factor (Fraction)	0.5
Lighting Technology	LED	Voltage (Nom)	220-240 V
		Ballast Compatibility	EM
Light Technical		Temperature	
Color Code	740 [CCT of 4000K]	T-Case Maximum (Nom)	60 °C
Beam Angle (Nom)	240 degree(s)		
Luminous Flux	1,600 lm	Controls and Dimming	
Color Designation	Cool White (CW)	Dimmable	No
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Mechanical and Housing	
Color Consistency	<7	Bulb Finish	Frosted
Color rendering index (CRI)	73	Bulb Material	Glass
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product Length	1,200 mm
		Bulb Shape	T8
Operating and Electrical		Net Weight (Piece)	0.170 kg
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

Ecofit Ledtubes T8

Approval and Application


Energy Saving Product	Yes
Suitable For Accent Lighting	No
Approval Marks	RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	16 kWh
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 °C to 45 °C

Product Data

Order product name	16W (36W) G13 Cool White Non-dimmable Linear tube
--------------------	--



Full product name	16W (36W) G13 Cool White Non-dimmable Linear tube
Full product code	871869652501200
Order code	929001184508
Material Nr. (12NC)	929001184508
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696525012
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696525029

Dimensional drawing



Product	D1	D2	A1	A2	A3	C	D
16W (36W) G13 Cool White Non-dimmable Linear tube	25.68 mm	28 mm	1,198 mm	1,205 mm	1,212 mm	1,212 mm	27.8 mm

Photometric data




Light Distribution Diagram - LEDtube 1200mm 16W 740 T8 AP C G

General uniform lighting - LEDtube 1200mm 16W 740 T8 AP C G


Ecofit Ledtubes T8

Photometric data




Spectral Power Distribution Colour - LEDtube 1200mm 16W 740 T8 AP C G


Lifetime




LEDtube 16W G13 740 T8 AP I G



LEDtube 16W G13 740 T8 AP I G




LEDtube 16W G13 740 T8 AP I G



Lumen Maintenance Diagram - LEDtube 1200mm 16W 740 T8 AP C G

Ecofit Ledtubes T8

Lifetime



Lumen Maintenance Diagram - LEDtube 1200mm 16W 740 T8 AP C G

