



# Ecofit Ledtubes T8

## 8W (18W) G13 Cool daylight Linear tube

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

### Product data

General Information		Starting Time (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Warm-up time to 60% light	0.5 s
Nominal lifetime	15,000 hour(s)	Power Factor (Fraction)	0.5
Switching Cycle	50,000	Voltage (Nom)	220-240 V
Rated Lifetime (Hours)	15,000 hour(s)	Ballast Compatibility	EM
Lighting Technology	LED	Temperature	
Light Technical		T-Case Maximum (Nom)	60 °C
Color Code	765 [CCT of 6500K]	Controls and Dimming	
Beam Angle (Nom)	240 degree(s)	Dimmable	No
Luminous Flux	800 lm	Mechanical and Housing	
Color Designation	Cool Daylight	Bulb Finish	Frosted
Correlated Color Temperature (Nom)	6500 K	Bulb Material	Glass
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Product Length	600 mm
Color Consistency	<7	Bulb Shape	T8
Color rendering index (CRI)	73	Net Weight (Piece)	0.090 kg
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application	
Operating and Electrical		Energy Saving Product	Yes
Line Frequency	50 to 60 Hz	Suitable For Accent Lighting	No
Input Frequency	50 to 60 Hz		
Power Consumption	8 W		

# Ecofit Ledtubes T8


Approval Marks	RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 °C to 45 °C

## Product Data

Order product name	8W (18W) G13 Cool daylight Linear tube
Full product name	8W (18W) G13 Cool daylight Linear tube



Full product code	871869652507400
Order code	929001184808
Material Nr. (12NC)	929001184808
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696525074
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696525081

## Dimensional drawing



Product	D1	D2	A1	A2	A3	C	D
8W (18W) G13	25.68	28 mm	588.5	595.5	602.5	602.5	27.8
Cool daylight	mm		mm	mm	mm	mm	mm
Linear tube							

## Photometric data




General uniform lighting - LEDtube 600mm 8W 765 T8 AP C G

Light Distribution Diagram - LEDtube 600mm 8W 765 T8 AP C G


# Ecofit Ledtubes T8

## Photometric data




Spectral Power Distribution Colour - LEDtube 600mm 8W 765 T8 AP C G


## Lifetime




LEDtube 16W G13 740 T8 AP I G



LEDtube 16W G13 740 T8 AP I G




LEDtube 16W G13 740 T8 AP I G



Lumen Maintenance Diagram - LEDtube 600mm 8W 765 T8 AP C G

## Ecofit Ledtubes T8

### Lifetime



Lumen Maintenance Diagram - LEDtube 600mm 8W 765 T8 AP C G

