



Essential LEDtube

LEDtube 600mm 8W 765 T8 AP I G

Essential LEDtube is an affordable LED tube that is suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data


General Information		Power Factor (Fraction)		0.5
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Voltage (Nom)	220-240 V	
Nominal lifetime	15,000 hour(s)	Ballast Compatibility	EM	
Switching Cycle	50,000	Temperature		
Lighting Technology	LED	T-Case Maximum (Nom)	60 °C	
Light Technical		Controls and Dimming		
Color Code	765 [CCT of 6500K]	Dimmable	No	
Beam Angle (Nom)	240 degree(s)	Mechanical and Housing		
Luminous Flux	800 lm	Bulb Finish	Frosted	
Color Designation	Cool Daylight	Bulb Material	Glass	
Correlated Color Temperature (Nom)	6500 K	Product Length	600 mm	
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Bulb Shape	T8	
Color Consistency	<7	Net Weight (Piece)	0.090 kg	
Color rendering index (CRI)	70	Approval and Application		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Saving Product	Yes	
Operating and Electrical		Suitable For Accent Lighting	No	
Line Frequency	50 to 60 Hz	Approval Marks	RoHS compliance KEMA Keur certificate	
Input Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h	8 kWh	
Power Consumption	8 W	EU RoHS compliant	Yes	
Starting Time (Nom)	0.5 s			
Warm-up time to 60% light	0.5 s			

Essential LEDtube

EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 °C to 45 °C
Product Data	
Order product name	LEDtube 600mm 8W 765 T8 AP I G
Full product name	LEDtube 600mm 8W 765 T8 AP I G
Full product code	871869664605200



Order code	929001184838
Material Nr. (12NC)	929001184838
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696646052
Numerator - Packs per outer box	20
EAN/UPC - Case	8718696646069

Dimensional drawing




Product	D1	D2	A1	A2	A3	C	D
LEDtube 600mm	25.68	28 mm	588.5	595.5	602.5	602.5	27.8
8W 765 T8 AP I G	mm		mm	mm	mm	mm	mm

Photometric data



General uniform lighting - LEDtube 600mm 8W 765 T8 AP I G


Light Distribution Diagram - LEDtube 600mm 8W 765 T8 AP I G



Spectral Power Distribution Colour - LEDtube 600mm 8W 765 T8 AP I G



Essential LEDtube

Lifetime




LEDtube 16W G13 740 T8 AP I G

LEDtube 16W G13 740 T8 AP I G



LEDtube 16W G13 740 T8 AP I G

Lumen Maintenance Diagram - LEDtube 600mm 8W 765 T8 AP I G



Lumen Maintenance Diagram - LEDtube 600mm 8W 765 T8 AP I G

Essential LEDtube

