



CorePro LEDspot MV



Corepro LEDspot 4.6-50W GU10 830 36D UK

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data


General Information			
Cap base	GU10	Power Consumption	4.6 W
Nominal lifetime	15,000 h	Lamp current (nom.)	39 mA
Switching Cycle	50,000	Wattage equivalent	50 W
Lighting Technology	LED	Starting time (nom.)	0.5 s
Light Technical		Warm-up time to 60% light	0.5 s
Colour Code	830 [CCT of 3000K]	Power Factor (Fraction)	0.5
Beam angle (nom.)	36 degree(s)	Voltage (nom.)	220-240 V
Luminous Flux	370 lm	Temperature	
Luminous intensity (nom.)	740 cd	T-Case maximum (nom.)	80 °C
Colour designation	White (WH)	Controls and Dimming	
Correlated Colour Temperature (Nom)	3000 K	Dimmable	No
Luminous efficacy (rated) (nom.)	80.00 lm/W	Mechanical and Housing	
Colour consistency	<6	Bulb shape	PAR16
Colour rendering index (CRI)	80	Net Weight (Piece)	0.045 kg
LLMF at end of nominal lifetime (nom.)	70 %	Approval and Application	
Luminous flux in 90° cone (rated)	370 lm	Energy Efficiency Class	F
Photobiological safety according to EN 62471	RG1	Suitable for accent lighting	Yes
Operating and Electrical		Energy consumption kWh/1,000 hours	5 kWh
Line Frequency	50 to 60 Hz	EPREL Registration Number	391858
Input frequency	50 to 60 Hz		

CorePro LEDspot MV

EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Application Conditions	
Can it be used in closed luminaires	No
Product Data	
Order product name	Corepro LEDspot 4.6-50W GU10 830 36D UK



Full product name	Corepro LEDspot 4.6-50W GU10 830 36D UK
Full EOC	871869672837601
Order code	72837601
Material no. (12 NC)	929001218199
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696728376
Numerator – packs per outer box	10
EAN/UPC – Case	8719514405974

Dimensional drawing



Product	D	C
Corepro LEDspot 4.6-50W GU10 830 36D UK	50 mm	54 mm

Photometric data




Spectral Power Distribution Colour - Corepro LEDspot 4.6-50W GU10 830 36D UK

Accent Lighting Spots - Corepro LEDspot 4.6-50W GU10 830 36D UK


CorePro LEDspot MV

Photometric data




Light Distribution Diagram - Corepro LEDspot 4.6-50W GU10 830 36D UK

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - Corepro LEDspot 4.6-50W GU10 830 36D UK

