



CorePro GLASS LED candles and lustres



CorePro LEDCandleND 2-25W E14B35 827CL G

Featuring a classic heritage design, these filament LED candles combine the familiar shapes of classic incandescent bulbs with the benefits of long-lasting LED technology. The LED candle bulb is a very easy choice for people who are looking for a retrofit LED replacement, it provides 90% energy savings compared with conventional lamps. CorePro Glass LED bulbs provide excellent quality of light for stairway lighting. The LED candle bulb offers a lifetime of 15,000 hours to reduce maintenance costs.

Product data


General Information	
Cap base	E14
Nominal lifetime	15,000 h
Switching Cycle	20,000
Lighting Technology	LED
Flux measurement reference	Sphere
Light Technical	
Colour Code	827 [CCT of 2700K]
Luminous Flux	250 lm
Colour designation	Warm White (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	125.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Photobiological safety according to EN 62471	RG1

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	2 W
Lamp current (nom.)	20 mA
Wattage equivalent	25 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	36 °C
Controls and Dimming	
Dimmable	No


CorePro GLASS LED candles and lustres

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	B35
Net Weight (Piece)	0.014 kg
Approval and Application	
Energy Efficiency Class	E
Energy-saving product	Yes
Suitable for accent lighting	No
Energy consumption kWh/1,000 hours	2 kWh
EPREL Registration Number	387351
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM)	1
Stroboscopic effect	0.4

Dimensional drawing




Photometric data



Spectral Power Distribution Colour - CorePro LEDCandleND 2-25W E14B35 827CL G

Application Conditions	
Can it be used in closed luminaires	No
Product Data	
Order product name	CorePro LEDCandleND 2-25W E14B35 827CL G
Full product name	CorePro LEDCandleND 2-25W E14B35 827CL G
Full EOC	871951437757800
Order code	37757800
Material no. (12 NC)	929001238392
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514377578
Numerator – packs per outer box	10
EAN/UPC - Case	8719514377585


Product	D	C
CorePro LEDCandleND 2-25W E14B35 827CL G	35 mm	97 mm



General uniform lighting - CorePro LEDCandleND 2-25W E14B35 827CL G


CorePro GLASS LED candles and lustres

Photometric data




Light Distribution Diagram - CorePro LEDCandleND 2-25W E14B35 827CL G

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - CorePro LEDCandleND 2-25W E14B35 827CL G

