



InstantFit (UL Type-A) T5

24T5HO/46-835/IF33/P/DIM 10/1

MasterClass, LEDtube, T5, 47-1/4 inch, 24 W, 3500 K, 3300 lm, 50000 hour(s)

The InstantFit TLED lamps provide hassle-free installation with simple lamp-for-lamp replacements. They deliver what we promise, with at least 40% energy savings, flicker-free performance, and the life you would expect. Other lamps claim compatibility but only InstantFit (UL Type-A) has been proven to work with over 200 ballasts and drivers, delivering even light output, with proven energy savings and a long average lifetime. End users will be delighted being under these comfortable and high quality InstantFit lamps with no visible flicker and optimized optics. Energy managers will enjoy the InstantFit lamps too as they can count the savings delivered by our lamps. To enjoy more energy savings, the InstantFit lamps can be paired with the Advance TLED drivers to create a Type C system.

Product data

General Information		Operating and Electrical	
Cap-Base	G5	Correlated Color Temperature (Nom)	3500 K
Nominal lifetime	50,000 hour(s)	Luminous Efficacy (rated) (Nom)	137.00 lm/W
Switching Cycle	50,000	Color Consistency	<5
Lighting Technology	LEDtube	Color rendering index (CRI)	82
		LLMF At End Of Nominal Lifetime (Nom)	70 %
Light Technical			
Color Code	835 [CCT of 3500K]	Line Frequency	40000-80000 Hz
Beam Angle (Nom)	160 degree(s)	Input Frequency	40000-80000 Hz
Luminous Flux	3,300 lm	Power Consumption	24 W
Color Designation	White (WH)	Lamp Current (Max)	600 mA

InstantFit (UL Type-A) T5

Lamp Current (Min)	400 mA
Wattage Equivalent	54 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	39-64 V
UL Type	UL Type A

Temperature

T-Case Maximum (Nom)	113 °F
----------------------	--------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	47-1/4 inch
Bulb Shape	T5
Net Weight (Piece)	0.375 lb

Approval and Application

Energy Saving Product	Yes
-----------------------	-----

Approval Marks	UL certificate RoHS compliance DLC compliance
Energy Certifications	DLC Standard
EU RoHS compliant	Yes
Ambient temperature range	-4 °F to 113 °F


Application Conditions

can it be used in closed luminaires	Yes
Wireless Technology	Not applicable

Product Data

Order product name	24T5HO/46-835/IF33/P/DIM 10/1
Full product name	24T5HO/46-835/IF33/P/DIM 10/1
Order code	467134
Material Nr. (12NC)	929001283804
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677467135
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677467130



Dimensional drawing



Product	D1	D2	A1	A2	A3
24T5HO/46-835/IF33/P/DIM 10/1	5/8 inch	3/4 inch	45-3/16 inch	45-1/2 inch	45-3/4 inch


InstantFit (UL Type-A) T5

Photometric data



Spectral Power Distribution Colour - 24T5HO/46-835/IF33/P/DIM 10/1

General uniform lighting - 24T5HO/46-835/IF33/P/DIM 10/1



Light Distribution Diagram - 24T5HO/46-835/IF33/P/DIM 10/1

