



Party Spot

13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF

LEDspot, PAR38, E26, 10950 hour(s), Glass

Philips 13.5-watt PAR 38s provide bright colorful light perfect for special occasions, parties and holidays. These PAR 38 lamps are available in up to four different colors and offer a festive touch to your home lighting. Brighten up your home and celebrate with color using these energy saving LED bulbs.

Product data

| General Information | |
|---------------------------------------|----------------|
| Cap-Base | E26 |
| Nominal lifetime | 10,950 hour(s) |
| Switching Cycle | 10,000 |
| Rated Lifetime (Hours) | 10,950 hour(s) |
| Lighting Technology | LEDspot |
| Light Technical | |
| Color Code | Yellow |
| Color Designation | Yellow |
| Color Consistency | <6 |
| Color rendering index (CRI) | - |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Line Frequency | 60 Hz |
| Input Frequency | 60 Hz |
| Power Consumption | 13.5 W |
| Lamp Current (Nom) | 165 mA |
| Starting Time (Nom) | 0.5 s |

| Warm-up time to 60% light | 0.5 s |
|-------------------------------------|--------------------|
| Power Factor (Fraction) | 0.5 |
| Voltage (Nom) | 120 V |
| UL Type | Yes |
| Temperature | |
| T-Case Maximum (Nom) | 65 °C |
| Controls and Dimming | |
| Dimmable | No |
| Mechanical and Housing | |
| Bulb Finish | Frosted |
| Bulb Material | Glass |
| Overall length | 132 mm |
| Overall width | 122 mm |
| Overall height | 132 mm |
| Dimensions (Height x Width x Depth) | 132 x 122 x 132 mm |
| Bulb Shape | PAR38 |
| UL Wet/ damp/ dry location | Wet location |

Party Spot

| | |
|--------------------|----------|
| Net Weight (Piece) | 0.350 kg |
|--------------------|----------|

Approval and Application

| | |
|------------------------------|-----------------|
| Suitable For Accent Lighting | Yes |
| EU RoHS compliant | Yes |
| EyeComfort | Yes |
| T20 compliant | N/A |
| LED Innovations | EyeComfort |
| Ambient temperature range | -20 °C to 45 °C |


Application Conditions

| | |
|-------------------------------------|----------------|
| can it be used in closed luminaires | Yes |
| Wireless Technology | Not applicable |

Product Data



| | |
|---------------------------------|---|
| Order product name | 13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF |
| Full product name | 13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF |
| Order code | 568279 |
| Material Nr. (12NC) | 929001306633 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677568276 |
| Numerator - Packs per outer box | 3 |
| EAN/UPC - Case | 50046677568271 |

Dimensional drawing



| Product | D | C |
|---|--------|--------|
| 13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF | 122 mm | 132 mm |

Photometric data





Light Distribution Diagram - 13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF

Accent Lighting Spots - 13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF

Party Spot

Lifetime



Lumen Maintenance Diagram - 13.5PAR38/PER/YELLOW/G/E26/ND/ULW
3/IPF

Life Expectancy Diagram

