



Party Spot

13.5PAR38/PER/GREEN/G/E26/ND/ULW 3/1PF

Philips 13.5-watt PAR 38s provide bright colorful light perfect for special occasions, parties and holidays. These PAR 38 lamps are available in up to four different colors and offer a festive touch to your home lighting. Brighten up your home and celebrate with color using these energy saving LED bulbs.

Product data

| General Information | |
|---------------------------------------|-----------------------------------|
| Cap-Base | E26 [Single Contact Medium Screw] |
| Nominal lifetime | 10,950 hour(s) |
| Switching Cycle | 10,000 |
| Rated Lifetime (Hours) | 10,950 hour(s) |
| Lighting Technology | LED |
| Light Technical | |
| Color Code | Green |
| Color Designation | Green |
| Color Consistency | <6 |
| Color rendering index (CRI) | - |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Line Frequency | 60 Hz |
| Input Frequency | 60 Hz |
| Power Consumption | 13.5 W |
| Lamp Current (Nom) | 165 mA |
| Starting Time (Nom) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.5 |
| Voltage (Nom) | 120 V |

| UL Type | Yes |
|------------------------------|-----------------|
| Temperature | |
| T-Case Maximum (Nom) | 149 °F |
| Controls and Dimming | |
| Dimmable | No |
| Mechanical and Housing | |
| Bulb Finish | Frosted |
| Bulb Material | Glass |
| Bulb Shape | PAR38 |
| UL Wet/ damp/ dry location | Wet location |
| Net Weight (Piece) | 0.772 lb |
| Approval and Application | |
| Suitable For Accent Lighting | Yes |
| EU RoHS compliant | Yes |
| EyeComfort | Yes |
| T20 compliant | N/A |
| LED Innovations | EyeComfort |
| Ambient temperature range | -4 °F to 113 °F |

Party Spot

Application Conditions


can it be used in closed luminaires Yes

Product Data

Order product name 13.5PAR38/PER/GREEN/G/E26/ND/ULW 3/1PF
 Full product name 13.5PAR38/PER/GREEN/G/E26/ND/ULW 3/1PF



Order code 568287
 Material Nr. (12NC) 929001306763
 Numerator - Quantity Per Pack 1
 EAN/UPC - Product/Case 046677568283
 Numerator - Packs per outer box 3
 EAN/UPC - Case 50046677568288

Dimensional drawing



| Product | D | C |
|--|--------------|------------|
| 13.5PAR38/PER/GREEN/G/E26/ND/ULW 3/1PF | 4-13/16 inch | 5-1/4 inch |

Photometric data





Light Distribution Diagram - 13.5PAR38/PER/GREEN/G/E26/ND/ULW 3/1PF

Accent Lighting Spots - 13.5PAR38/PER/GREEN/G/E26/ND/ULW 3/1PF

Party Spot

Lifetime



Lumen Maintenance Diagram - 13.5PAR38/PER/GREEN/G/E26/ND/ULW
3/IPF

Life Expectancy Diagram

