



# Classic filament LED candles and lusters

## LEDclassic 40W B35 2700K E14 ND FR AU

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

### Product data

General Information	
Cap-Base	E14
Nominal lifetime	15,000 h
Switching Cycle	15,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
Light Technical	
Color Code	827 [CCT of 2700K]
Color Code	827 [CCT of 2700K]
Luminous Flux	470 lm
Color Designation	Warm White (WW)
Luminous Efficacy (rated) (Nom)	134 lm/W
Correlated Color Temperature (Nom)	2700 K
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz

Power Consumption	3.5 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.4 s
Warm-up time to 60% light	0.4 s
Power Factor (Fraction)	0.51
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Bulb Shape	B35

# Classic filament LED candles and lusters

## Approval and Application


Energy Consumption kWh/1000 h	5 kWh
EU RoHS compliant	Yes

## Product Data

Order product name	LEDclassic 40W B35 2700K E14 ND FR AU
Full product name	LEDclassic 40W B35 2700K E14 ND FR AU
Full product code	871951437749300
Order code	929001345380



Material Nr. (12NC)	929001345380
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.014 kg
EAN/UPC - Product/Case	8719514377493
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514377509

## Dimensional drawing




Product	D	C
LEDclassic 40W B35 2700K E14 ND FR AU	35 mm	97 mm

## Photometric data



Spectral Power Distribution Colour - LEDclassic 40W B35 2700K E14 ND FR AU



General uniform lighting - LEDclassic 40W B35 2700K E14 ND FR AU



Light Distribution Diagram - LEDclassic 40W B35 2700K E14 ND FR AU

# Classic filament LED candles and lusters

## Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LEDclassic 40W B35 2700K E14 ND FR AU

