



Classic filament LED candles and lusters

LEDclassic 40W P45 2700K E27 ND FR AU

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 h
Switching Cycle	15,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	134 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %


Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	3.5 W
Lamp Current (Nom)	35 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.51
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass

Classic filament LED candles and lusters

Bulb Shape	P45 [P 45mm]
Approval and Application	
Energy Consumption kWh/1000 h	5 kWh
Product Data	
Order product name	LEDclassic 40W P45 2700K E27 ND FR AU
Full product name	LEDclassic 40W P45 2700K E27 ND FR AU
Full product code	871951438825300
Local code description	LED40P45E27WWFR



Order code	929001345780
Material Nr. (12NC)	929001345780
Local order code	LED40P45E27WWFR
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514388253
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514388260

Dimensional drawing



Product	D	C
LEDclassic 40W P45 2700K E27 ND FR AU	45 mm	78 mm

Photometric data




Spectral Power Distribution Colour - LEDclassic 40W P45 2700K E27 ND FR AU

General uniform lighting - LEDclassic 40W P45 2700K E27 ND FR AU


Classic filament LED candles and lusters

Photometric data




Light Distribution Diagram - LEDclassic 40W P45 2700K E27 ND FR AU

Lifetime



Life Expectancy Diagram - LEDclassic 40W P45 2700K E27 ND FR AU



Lumen Maintenance Diagram - LEDclassic 40W P45 2700K E27 ND FR AU

