



# CorePro LED linear MV



## CorePro LED linear D 14-120W R7S 118 830

CorePro, LEDspot, R7S, 120 W, R7s, 3000 K, 2000 lm, CRI 80, 15000 h, Plastic

CorePro R7S is a retrofit replacement for traditional double-ended linear R7S lamps. Its 'light all around' design delivers light that is just like a halogen lamp. Within the range, you can choose dimmable products which have deep a dimming function that enables a cosy ambience when using a dimmable fixture.

### Product data

General Information	
Cap base	R7s
Nominal lifetime	15,000 h
Switching Cycle	50,000
Lighting Technology	LEDspot
Warranty period	2 years

Light Technical	
Colour Code	830 [CCT of 3000K]
Luminous Flux	2,000 lm
Colour designation	White (WH)
Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	142.86 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	14 W
Lamp current (nom.)	75 mA
Wattage equivalent	120 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (nom.)	220-240 V

Temperature	
T-Case maximum (nom.)	100 °C

Controls and Dimming	
Dimmable	Only with specific dimmers

# CorePro LED linear MV

## Mechanical and Housing

Lamp Finish	Clear
Bulb material	Plastic
Bulb shape	R7S
Net Weight (Piece)	0.095 kg

## Approval and Application

Energy Efficiency Class	D
Energy consumption kWh/1,000 hours	14 kWh
EPREL Registration Number	397582
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Ambient temperature range	-20°C to 45°C


## Application Conditions

Can it be used in closed luminaires	No
-------------------------------------	----

## Product Data


Order product name	CorePro LED linear D 14-120W R7S 118 830
Full product name	CorePro LED linear D 14-120W R7S 118 830
Full EOC	871869671400300
Order code	929001353602
Material no. (12 NC)	929001353602
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696714003
Numerator – packs per outer box	10
EAN/UPC – Case	8718696714010

## Dimensional drawing




Product	D	C
CorePro LED linear D 14-120W R7S 118 830	29 mm	118 mm

## Photometric data



General uniform lighting - CorePro LED linear D 14-120W R7S 118 830



Spectral Power Distribution Colour - CorePro LED linear D 14-120W R7S 118 830

