



CorePro LED linear MV



CorePro LED linear D 14-120W R7S 118 840

CorePro, LEDspot, R7S, 120 W, R7s, 4000 K, 2000 lm, CRI 80, 15000 h, Plastic

CorePro R7S is a retrofit replacement for traditional double-ended linear R7S lamps. Its 'light all around' design delivers light that is just like a halogen lamp. Within the range, you can choose dimmable products which have deep a dimming function that enables a cosy ambience when using a dimmable fixture.

Product data

General Information	
Cap base	R7s
Nominal lifetime	15,000 h
Switching Cycle	50,000
Lighting Technology	LEDspot
Warranty period	2 years

Light Technical	
Colour Code	840 [CCT of 4000K]
Luminous Flux	2,000 lm
Colour designation	Cool White (CW)
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	142.86 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	14 W
Lamp current (nom.)	75 mA
Wattage equivalent	120 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (nom.)	220-240 V

Temperature	
T-Case maximum (nom.)	100 °C

Controls and Dimming	
Dimmable	Only with specific dimmers

CorePro LED linear MV

Mechanical and Housing

Lamp Finish	Clear
Bulb material	Plastic
Bulb shape	R7S
Net Weight (Piece)	0.095 kg

Approval and Application

Energy Efficiency Class	D
Energy consumption kWh/1,000 hours	14 kWh
EPREL Registration Number	397583
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Ambient temperature range	-20°C to 45°C


Application Conditions

Can it be used in closed luminaires	No
-------------------------------------	----

Product Data



Order product name	CorePro LED linear D 14-120W R7S 118 840
Full product name	CorePro LED linear D 14-120W R7S 118 840
Full EOC	871869671406500
Order code	929001353702
Material no. (12 NC)	929001353702
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696714065
Numerator – packs per outer box	10
EAN/UPC – Case	8718696714072

Dimensional drawing



Product	D	C
CorePro LED linear D 14-120W R7S 118 840	29 mm	118 mm

Photometric data




General uniform lighting - CorePro LED linear D 14-120W R7S 118 840

Spectral Power Distribution Colour - CorePro LED linear D 14-120W R7S 118 840

General uniform lighting - CorePro LED linear D 14-120W R7S 118 840


CorePro LED linear MV

Photometric data




Light Distribution Diagram - CorePro LED linear D 14-120W R7S 118 840

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - CorePro LED linear D 14-120W R7S 118 840

