



CorePro Glass LED bulbs



CorePro LEDBulbND 7-60W E27 ST64 827CL G

Featuring a classic heritage design, these filament LED lamps combine the familiar shapes of classic incandescent bulbs with the benefits of long-lasting LED technology. A very easy choice for people who are looking for a retrofit LED replacement, these CorePro LED bulbs provide 90% energy savings compared with conventional lamps. CorePro Glass LED bulbs provide excellent quality of light in a vintage style. CorePro LED lighting that offers a lifetime of 15,000 hours to reduce maintenance costs.

Product data


General Information		Photobiological safety according to EN 62471 RG1	
Cap base	E27		
Nominal lifetime	15,000 h		
Switching Cycle	20,000		
Lighting Technology	LED		
Flux measurement reference	Sphere		
Light Technical		Operating and Electrical	
Colour Code	827 [CCT of 2700K]	Line Frequency	50 to 60 Hz
Beam angle (nom.)	300 degree(s)	Input frequency	50 to 60 Hz
Luminous Flux	806 lm	Power Consumption	7 W
Colour designation	Warm White (WW)	Lamp current (nom.)	60 mA
Correlated Colour Temperature (Nom)	2700 K	Wattage equivalent	60 W
Luminous efficacy (rated) (nom.)	115.00 lm/W	Starting time (nom.)	0.5 s
Colour consistency	<6	Warm-up time to 60% light	0.5 s
Colour rendering index (CRI)	80	Power Factor (Fraction)	0.51
LLMF at end of nominal lifetime (nom.)	70 %	Voltage (nom.)	220-240 V
		Temperature	
		T-Case maximum (nom.)	45 °C

CorePro Glass LED bulbs

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	ST64
Net Weight (Piece)	0.048 kg
Approval and Application	
Energy Efficiency Class	E
Energy consumption kWh/1,000 hours	7 kWh
EPREL Registration Number	1825163
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM)	1
Stroboscopic effect	0.9



Application Conditions	
Can it be used in closed luminaires	No
Product Data	
Order product name	CorePro LEDBulbND 7-60W E27 ST64 827CL G
Full product name	CorePro LEDBulbND 7-60W E27 ST64 827CL G
Full EOC	871951434675800
Order code	34675800
Material no. (12 NC)	929001387692
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514346758
Numerator – packs per outer box	10
EAN/UPC – Case	8719514346765

Dimensional drawing



Product	D	C
CorePro LEDBulbND 7-60W E27 ST64 827CL G	64 mm	140 mm

Photometric data




General uniform lighting - CorePro LEDBulbND 7-60W E27 ST64 827CL G

Spectral Power Distribution Colour - CorePro LEDBulbND 7-60W E27 ST64 827CL G


CorePro Glass LED bulbs

Photometric data




Light Distribution Diagram - CorePro LEDBulbND 7-60W E27 ST64 827CL G

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - CorePro LEDBulbND 7-60W E27 ST64 827CL G

