



CorePro Glass LED bulbs

CorePro LEDBulbND 7-60W E27 G93 827 CL G

CorePro, LEDbulb, G93, 60 W, E27, 2700 K, 806 lm, CRI 80, 15000 h, Glass

Featuring a classic heritage design, these filament LED lamps combine the familiar shapes of classic incandescent bulbs with the benefits of long-lasting LED technology. A very easy choice for people who are looking for a retrofit LED replacement, these CorePro LED bulbs provide 90% energy savings compared with conventional lamps. CorePro Glass LED bulbs provide excellent quality of light in a vintage style. CorePro LED lighting that offers a lifetime of 15,000 hours to reduce maintenance costs.

Product data


General Information		Luminous efficacy (rated) (nom.)	
Cap base	E27		115.00 lm/W
Nominal lifetime	15,000 h	Colour consistency	<6
Switching Cycle	20,000	Colour rendering index (CRI)	80
Lighting Technology	LEDbulb	LLMF at end of nominal lifetime (nom.)	70 %
Flux measurement reference	Sphere	Photobiological safety according to EN 62471	RG1
Warranty period	2 years		
Light Technical		Operating and Electrical	
Colour Code	827 [CCT of 2700K]	Line Frequency	50 to 60 Hz
Beam angle (nom.)	300 degree(s)	Input frequency	50 to 60 Hz
Luminous Flux	806 lm	Power Consumption	7 W
Colour designation	Warm White (WW)	Lamp current (nom.)	60 mA
Correlated Colour Temperature (Nom)	2700 K	Wattage equivalent	60 W
		Starting time (nom.)	0.5 s
		Warm-up time to 60% light	0.5 s

CorePro Glass LED bulbs

Power Factor (Fraction)	0.51
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	45 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Clear
Bulb material	Glass
Bulb shape	G93
Net Weight (Piece)	0.070 kg
Approval and Application	
Energy Efficiency Class	E
Energy consumption kWh/1,000 hours	7 kWh
EPREL Registration Number	1825194
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes

Flickering value (PstLM)	1
Stroboscopic effect	0.4
Ambient temperature range	-20 to +45 °C
Application Conditions	
Can it be used in closed luminaires	No
Wireless Technology	Not applicable
Product Data	
Order product name	CorePro LEDBulbND 7-60W E27 G93 827 CL G
Full product name	CorePro LEDBulbND 7-60W E27 G93 827 CL G
Full EOC	871951434677200
Order code	929001387992
Material no. (12 NC)	929001387992
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514346772
Numerator – packs per outer box	6
EAN/UPC - Case	8719514346789



Dimensional drawing



Product	D	C
CorePro LEDBulbND 7-60W E27 G93 827 CL G	95 mm	140 mm


CorePro Glass LED bulbs

Photometric data




General uniform lighting - CorePro LEDBulbND 7-60W E27 G93 827 CL G

Spectral Power Distribution Colour - CorePro LEDBulbND 7-60W E27 G93 827 CL G




Light Distribution Diagram - CorePro LEDBulbND 7-60W E27 G93 827 CL G

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - CorePro LEDBulbND 7-60W E27 G93 827 CL G

CorePro Glass LED bulbs

