



# PL-C/T

## 8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1

CorePro, LED, PL-C;PL-T, 8.5 W, 2700 K, 850 lm, 50000 hour(s)

Philips PLED 4-pin & 2-pin lamps are an affordable LED solution to replace compact fluorescent lamps. The product provides a natural lighting effect for use in many lighting applications, and provides instant energy savings, making them an environmentally-friendly solution. Available as replacements for 13W, 26W and 32W compact fluorescent lamps.

### Product data

General Information		Power Consumption	
Cap-Base	G24q	Lamp Current (Max)	550 mA
Nominal lifetime	50,000 hour(s)	Lamp Current (Min)	150 mA
Switching Cycle	50,000	Wattage Equivalent	26 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
Light Technical		Warm-up time to 60% light	0.5 s
Color Code	827 [CCT of 2700K]	Power Factor (Fraction)	0.9
Beam Angle (Nom)	120 degree(s)	Voltage (Nom)	120 V
Luminous Flux	850 lm	UL Type	UL Type A
Color Designation	Warm White (WW)	Temperature	
Correlated Color Temperature (Nom)	2700 K	T-Case Maximum (Nom)	60 °C
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Controls and Dimming	
Color Consistency	<6	Dimmable	Yes
Color rendering index (CRI)	82	Mechanical and Housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Finish	Frosted
Operating and Electrical		Bulb Material	Plastic
Line Frequency	20000-100000 Hz	Product Length	148 mm
Input Frequency	20000-100000 Hz		

PL-C/T

Bulb Shape	PL-C;PL-T
Net Weight (Piece)	0.082 kg

Approval and Application


Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate KEMA Keur certificate DLC compliance
Energy Certifications	DLC Standard
EU RoHS compliant	Yes
Ambient temperature range	-20 °C to 45 °C

Application Conditions

can it be used in closed luminaires	Yes
-------------------------------------	-----


Product Data	
Order product name	8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1
Full product name	8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1
Order code	458364
Material Nr. (12NC)	929001388004
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677458362
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677472554

Dimensional drawing




Product	D1	D	A1	A2	A3
8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1	34 mm	34 mm	129 mm	148 mm	164 mm

Photometric data




Spectral Power Distribution Colour - 8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1




General uniform lighting - 8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1

Photometric data




Light Distribution Diagram - 8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1


Lifetime




LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm



Lumen Maintenance Diagram - 8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1




LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm



LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm

Lifetime



Lumen Maintenance Diagram - 8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM  
10/1

