



PL-C/T

8.5PL-C/T/COR/26H-840/IF9/P/4P/DIM 10/1

CorePro, LED, PL-C;PL-T, 5-7/8 inch, 8.5 W, 4000 K, 950 lm, 50000 hour(s)

CorePro, LED, PL-C;PL-T, 5-7/8 inch, 8.5 W, 4000 K, 950 lm, 50000 hour(s), 111.00 lm/W, G24q Rotatable end-cap, Plastic

Product data

General Information	
Cap-Base	G24q Rotatable end-cap
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	120 degree(s)
Luminous Flux	950 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	111.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	20000-100000 Hz
Input Frequency	20000-100000 Hz
Power Consumption	8.5 W

Lamp Current (Max)	550 mA
Lamp Current (Min)	150 mA
Wattage Equivalent	26 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V
UL Type	UL Type A
Temperature	
T-Case Maximum (Nom)	140 °F
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	5-7/8 inch
Bulb Shape	PL-C;PL-T

PL-C/T

Net Weight (Piece)	0.181 lb
--------------------	----------

Approval and Application


Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate KEMA Keur certificate DLC compliance
Energy Certifications	DLC Standard
EU RoHS compliant	Yes
Ambient temperature range	-4 °F to 113 °F

Application Conditions

can it be used in closed luminaires	Yes
Wireless Technology	Not applicable


Product Data	
Order product name	8.5PL-C/T/COR/26H-840/IF9/P/4P/DIM 10/1
Full product name	8.5PL-C/T/COR/26H-840/IF9/P/4P/DIM 10/1
Order code	458398
Material Nr. (12NC)	929001388304
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677458393
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677472783

Dimensional drawing




Product	D1	D	A1	A2	A3
8.5PL-C/T/COR/ 26H-840/IF9/P/4P/DIM 10/1	1-3/8 inch	1-3/8 inch	5-1/8 inch	5-7/8 inch	6-1/2 inch

Photometric data




Spectral Power Distribution Colour - 8.5PL-C/T/COR/26H-840/IF9/P/4P/DIM 10/1




General uniform lighting - 8.5PL-C/T/COR/26H-840/IF9/P/4P/DIM 10/1

Photometric data




Light Distribution Diagram - 8.5PL-C/T/COR/26H-840/IF9/P/4P/DIM 10/1


Lifetime




LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm



Lumen Maintenance Diagram - 8.5PL-C/T/COR/26H-840/IF9/P/4P/DIM 10/1




LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm



LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm

Lifetime



Lumen Maintenance Diagram - 8.5PL-C/T/COR/26H-840/IF9/P/4P/DIM
10/1

