

# PHILIPS

## Lighting



## PL-C/T

### 10.5PL-C/T/COR/26V-827/IF12/P/4P/DIM10/1

CorePro, LED, PL-C;PL-T, 110 mm, 10.5 W, 2700 K, 1200 lm, 50000 hour(s)

Philips PLED 4-pin & 2-pin lamps are an affordable LED solution to replace compact florescent lamps. The product provides a natural lighting effect for use in many lighting applications, and provides instant energy savings, making them an environmentally-friendly solution. Available as replacements for 13W, 26W and 32W compact fluorescent lamps.

#### Product data

General Information	
Cap-Base	GX24q
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED

Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	120 degree(s)
Luminous Flux	1,200 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	114.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	20000-100000 Hz
Input Frequency	20000-100000 Hz
Power Consumption	10.5 W
Lamp Current (Max)	550 mA
Lamp Current (Min)	150 mA
Wattage Equivalent	26 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V
UL Type	UL Type A


  

Temperature	
T-Case Maximum (Nom)	60 °C

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	110 mm
Bulb Shape	PL-C;PL-T
Net Weight (Piece)	0.091 kg
Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate KEMA Keur certificate DLC compliance
Energy Certifications	DLC Standard
EU RoHS compliant	Yes



Ambient temperature range	-20 °C to 45 °C
Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	10.5PL-C/T/COR/26V-827/IF12/P/4P/DIM10/1
Full product name	10.5PL-C/T/COR/26V-827/IF12/P/4P/DIM10/1
Order code	458406
Material Nr. (12NC)	929001388404
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677458409
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677472790

## Dimensional drawing



Product	D1	D	A1	A2	A3
10.5PL-C/T/COR/26V-827/IF12/P/4P/ DIM10/1	50 mm	50 mm	13 mm	110 mm	125 mm


## Photometric data







Spectral Power Distribution Colour - 10.5PL-C/T/COR/26V-827/IF12/P/4P/  
DIM10/1

General uniform lighting - 10.5PL-C/T/COR/26V-827/IF12/P/4P/DIM10/1


## Photometric data



## Lifetime



## Lifetime



Lumen Maintenance Diagram - 10.5PL-C/T/COR/26V-827/IF12/P/4P/  
DIM10/1

