



PL-C/T

10.5PL-C/T/COR/26V-840/IF13/P/4P/DIM10/1

Philips PLED 4-pin & 2-pin lamps are an affordable LED solution to replace compact fluorescent lamps. The product provides a natural lighting effect for use in many lighting applications, and provides instant energy savings, making them an environmentally-friendly solution. Available as replacements for 13W, 26W and 32W compact fluorescent lamps.

Product data


General Information	
Cap-Base	GX24q
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	120 degree(s)
Luminous Flux	1,300 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	123.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	20000-100000 Hz
Input Frequency	20000-100000 Hz
Power Consumption	10.5 W
Lamp Current (Max)	550 mA

Lamp Current (Min)	150 mA
Wattage Equivalent	26 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V
UL Type	UL Type A
Temperature	
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	110 mm
Bulb Shape	PL-C;PL-T
Net Weight (Piece)	0.091 kg

Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate KEMA Keur certificate DLC compliance
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	DLC Standard
EU RoHS compliant	Yes
Ambient temperature range	-20 °C to 45 °C
Application Conditions	
can it be used in closed luminaires	Yes


Product Data	
Order product name	10.5PL-C/T/COR/26V-840/IF13/P/4P/DIM10/1
Full product name	10.5PL-C/T/COR/26V-840/IF13/P/4P/DIM10/1
Order code	458430
Material Nr. (12NC)	929001388704
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677458430
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677472820

Dimensional drawing




Product	D1	D	A1	A2	A3
10.5PL-C/T/COR/26V-840/IF13/P/4P/ DIM10/1	50 mm	50 mm	13 mm	110 mm	125 mm

Photometric data




Spectral Power Distribution Colour - 10.5PL-C/T/COR/26V-840/IF13/P/4P/
DIM10/1




General uniform lighting - 10.5PL-C/T/COR/26V-840/IF13/P/4P/DIM10/1

Photometric data




Light Distribution Diagram - 10.5PL-C/T/COR/26V-840/IF13/P/4P/DIM10/1


Lifetime




LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm



LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm




Lumen Maintenance Diagram - 10.5PL-C/T/COR/26V-840/IF13/P/4P/DIM10/1



LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm

Lifetime



Lumen Maintenance Diagram - 10.5PL-C/T/COR/26V-840/IF13/P/4P/
DIM10/1

