



InstantFit (UL Type-A) T5

8T5HE/22-830/IF10/G/DIM 10/1

CorePro, LEDtube, T5, 23-5/8 inch, 8 W, 3000 K, 1000 lm, 50000 hour(s)

CorePro, LEDtube, T5, 23-5/8 inch, 8 W, 3000 K, 1000 lm, 50000 hour(s), 125.00 lm/W, G5, Glass

Product data

General Information			
Cap-Base	G5	Input Frequency	40000-110000 Hz
Nominal lifetime	50,000 hour(s)	Power Consumption	8 W
Switching Cycle	50,000	Lamp Current (Max)	400 mA
Lighting Technology	LEDtube	Lamp Current (Min)	60 mA
		Wattage Equivalent	14 W
		Starting Time (Nom)	0.5 s
		Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.9
		Voltage (Nom)	40-60 V
		UL Type	UL Type A
Light Technical		Temperature	
Color Code	830 [CCT of 3000K]	T-Case Maximum (Nom)	158 °F
Beam Angle (Nom)	200 degree(s)		
Luminous Flux	1,000 lm	Controls and Dimming	
Color Designation	White (WH)	Dimmable	Yes
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	125.00 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Frosted
Color rendering index (CRI)	82		
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Line Frequency	40000-110000 Hz		

InstantFit (UL Type-A) T5

Bulb Material	Glass
Product Length	23-5/8 inch
Bulb Shape	T5
Net Weight (Piece)	0.176 lb

Approval and Application

Energy Saving Product	Yes
Approval Marks	UL certificate RoHS compliance
EU RoHS compliant	Yes
Ambient temperature range	-4 °F to 113 °F

Application Conditions


can it be used in closed luminaires	Yes
-------------------------------------	-----

Wireless Technology	Not applicable
---------------------	----------------

Product Data



Order product name	8T5HE/22-830/IF10/G/DIM 10/1
Full product name	8T5HE/22-830/IF10/G/DIM 10/1
Order code	476416
Material Nr. (12NC)	929001823104
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677476410
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677476415

Dimensional drawing



Product	D1	D2	A1	A2	A3
8T5HE/22-830/IF10/G/DIM 10/1	5/8 inch	3/4 inch	21-9/16 inch	21-7/8 inch	22-1/8 inch

Photometric data



General uniform lighting - 8T5HE/22-830/IF10/G/DIM 10/1

Light Distribution Diagram - 8T5HE/22-830/IF10/G/DIM 10/1


InstantFit (UL Type-A) T5

Photometric data




Spectral Power Distribution Colour - 8T5HE/22-830/IF10/G/DIM 10/1


Lifetime




LEDtube 8-14W G5 830-850 200D DIM IF10-21



LEDtube 8-14W G5 830-850 200D DIM IF10-21




LEDtube 8-14W G5 830-850 200D DIM IF10-21



Lumen Maintenance Diagram - 8T5HE/22-830/IF10/G/DIM 10/1

InstantFit (UL Type-A) T5

Lifetime



Lumen Maintenance Diagram - 8T5HE/22-830/IF10/G/DIM 10/1

