

InstantFit (UL Type-A) T5

11T5HE/34-840/IF15/G/DIM 10/1

CorePro, LEDtube, T5, 35-7/16 inch, 11 W, 4000 K, 1500 lm, 50000 hour(s)

CorePro, LEDtube, T5, 35-7/16 inch, 11 W, 4000 K, 1500 lm, 50000 hour(s), 136.00 lm/W, G5, Glass

Product data

General Information			
Cap-Base	G5	Input Frequency	40000-110000 Hz
Nominal lifetime	50,000 hour(s)	Power Consumption	11 W
Switching Cycle	50,000	Lamp Current (Max)	400 mA
Lighting Technology	LEDtube	Lamp Current (Min)	60 mA
		Wattage Equivalent	21 W
		Starting Time (Nom)	0.5 s
		Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.9
		Voltage (Nom)	50-80 V
		UL Type	UL Type A
Light Technical		Temperature	
Color Code	840 [CCT of 4000K]	T-Case Maximum (Nom)	158 °F
Beam Angle (Nom)	200 degree(s)		
Luminous Flux	1,500 lm	Controls and Dimming	
Color Designation	Cool White (CW)	Dimmable	Yes
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	136.00 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Frosted
Color rendering index (CRI)	82		
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Line Frequency	40000-110000 Hz		

InstantFit (UL Type-A) T5

Bulb Material	Glass
Product Length	35-7/16 inch
Bulb Shape	T5
Net Weight (Piece)	0.243 lb

Approval and Application

Energy Saving Product	Yes
Approval Marks	UL certificate RoHS compliance
EU RoHS compliant	Yes
Ambient temperature range	-4 °F to 113 °F

Application Conditions


can it be used in closed luminaires	Yes
-------------------------------------	-----

Wireless Technology	Not applicable
---------------------	----------------

Product Data


Order product name	11T5HE/34-840/IF15/G/DIM 10/1
Full product name	11T5HE/34-840/IF15/G/DIM 10/1
Order code	476473
Material Nr. (12NC)	929001823704
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677476472
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677476477

Dimensional drawing




Product	D1	D2	A1	A2	A3
11T5HE/34-840/ IF15/G/DIM 10/1	5/8 inch	3/4 inch	33-3/8 inch	33-11/16 inch	33-15/16 inch

Photometric data




Spectral Power Distribution Colour - 11T5HE/34-840/IF15/G/DIM 10/1



General uniform lighting - 11T5HE/34-840/IF15/G/DIM 10/1


InstantFit (UL Type-A) T5

Photometric data




Light Distribution Diagram - 11T5HE/34-840/IF15/G/DIM 10/1


Lifetime




LEDtube 8-14W G5 830-850 200D DIM IF10-21



LEDtube 8-14W G5 830-850 200D DIM IF10-21




LEDtube 8-14W G5 830-850 200D DIM IF10-21



Lumen Maintenance Diagram - 11T5HE/34-840/IF15/G/DIM 10/1

InstantFit (UL Type-A) T5

Lifetime



Lumen Maintenance Diagram - 11T5HE/34-840/IF15/G/DIM 10/1

