

InstantFit (UL Type-A) T5

11T5HE/34-850/IF15/G/DIM 10/1

CorePro, LEDtube, T5, 35-7/16 inch, 11 W, 5000 K, 1500 lm, 50000 hour(s)

CorePro, LEDtube, T5, 35-7/16 inch, 11 W, 5000 K, 1500 lm, 50000 hour(s), 136.00 lm/W, G5, Glass

Product data

General Information	
Cap-Base	G5
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDtube
Light Technical	
Color Code	850 [CCT of 5000K]
Beam Angle (Nom)	200 degree(s)
Luminous Flux	1,500 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	136.00 lm/W
Color Consistency	<5
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	40000-110000 Hz

Input Frequency	40000-110000 Hz
Power Consumption	11 W
Lamp Current (Max)	400 mA
Lamp Current (Min)	60 mA
Wattage Equivalent	21 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	50-80 V
UL Type	UL Type A
Temperature	
T-Case Maximum (Nom)	158 °F
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted

InstantFit (UL Type-A) T5

Bulb Material	Glass
Product Length	35-7/16 inch
Bulb Shape	T5
Net Weight (Piece)	0.243 lb

Approval and Application

Energy Saving Product	Yes
Approval Marks	UL certificate RoHS compliance
EU RoHS compliant	Yes
Ambient temperature range	-4 °F to 113 °F

Application Conditions


can it be used in closed luminaires	Yes
-------------------------------------	-----

Wireless Technology	Not applicable
---------------------	----------------

Product Data



Order product name	11T5HE/34-850/IF15/G/DIM 10/1
Full product name	11T5HE/34-850/IF15/G/DIM 10/1
Order code	476481
Material Nr. (12NC)	929001823804
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677476489
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677476484

Dimensional drawing



Product	D1	D2	A1	A2	A3
11T5HE/34-850/ IF15/G/DIM 10/1	5/8 inch	3/4 inch	33-3/8 inch	33-11/16 inch	33-15/16 inch

Photometric data




General uniform lighting - 11T5HE/34-850/IF15/G/DIM 10/1

Light Distribution Diagram - 11T5HE/34-850/IF15/G/DIM 10/1


InstantFit (UL Type-A) T5

Photometric data




Spectral Power Distribution Colour - 11T5HE/34-850/IF15/G/DIM 10/1


Lifetime




LEDtube 8-14W G5 830-850 200D DIM IF10-21



LEDtube 8-14W G5 830-850 200D DIM IF10-21




LEDtube 8-14W G5 830-850 200D DIM IF10-21



Lumen Maintenance Diagram - 11T5HE/34-850/IF15/G/DIM 10/1

InstantFit (UL Type-A) T5

Lifetime



Lumen Maintenance Diagram - 11T5HE/34-850/IF15/G/DIM 10/1

