



LED BR30

7.2BR30/MAS/922-27/P/E26/WG 6/1FB

MasterClass, LEDbulb, BR30, 65 W, E26, 2200 K, 2700 K, 650 lm, 15000 hour(s), Plastic

MasterClass, LEDbulb, BR30, 65 W, E26, 2200 K, 2700 K, 650 lm, 15000 hour(s), Plastic, 90.00 lm/W

Product data

General Information	
Cap-Base	E26
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb
Light Technical	
Color Code	922-927 [CCT of 2200K-2700K]
Beam Angle (Nom)	110 degree(s)
Luminous Flux	650 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2200 2700 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	7.2 W


Lamp Current (Nom)	85 mA
Wattage Equivalent	65 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	167 °F
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	BR30
UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.121 lb

LED BR30

Approval and Application	
EU RoHS compliant	Yes
T20 compliant	Yes
Ambient temperature range	-4 to +113 °F
Application Conditions	
can it be used in closed luminaires	Yes
Wireless Technology	Not applicable
Product Data	
Order product name	7.2BR30/MAS/922-27/P/E26/WG 6/1FB



Full product name	7.2BR30/MAS/922-27/P/E26/WG 6/1FB
Order code	457044
Material Nr. (12NC)	929001870334
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677457044
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677457049

Dimensional drawing



Product	D	C
7.2BR30/MAS/922-27/P/E26/WG 6/1FB	3-3/4 inch	5-1/4 inch

Photometric data




Accent Lighting Spots - 7.2BR30/MAS/922-27/P/E26/WG 6/1FB

Light Distribution Diagram - 7.2BR30/MAS/922-27/P/E26/WG 6/1FB


LED BR30

Photometric data




Spectral Power Distribution Colour - 7.2BR30/MAS/922-27/P/E26/WG 6/1FB

Lifetime



Lumen Maintenance Diagram - 7.2BR30/MAS/922-27/P/E26/WG 6/1FB



LEDBulbs BR30 120V 19-120W 1200lm 2700K E26 D

