



Specialty Lamps

4A19/PER/RED/G/E26/ND 4/1PF

Philips A shape party lamp provides a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays. Philips Dusk to Dawn A19 lamp is equipped with a built-in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises. Philips 3-Way A shape lamps provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

Product data

General Information		Warm-up time to 60% light	
Cap-Base	E26 [Single Contact Medium Screw]	Power Factor (Fraction)	0.5 s
Nominal lifetime	15,000 hour(s)	Voltage (Nom)	0.40
Switching Cycle	20,000		120 V
Rated Lifetime (Hours)	15,000 hour(s)	Temperature	
Lighting Technology	LED	T-Case Maximum (Nom)	257 °F
Light Technical		Controls and Dimming	
Color Code	Red	Dimmable	No
Beam Angle (Nom)	330 degree(s)	Mechanical and Housing	
Color Designation	Red	Bulb Finish	Red
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Material	Glass
Operating and Electrical		Bulb Shape	A19
Line Frequency	60 Hz	UL Wet/ damp/ dry location	Wet location
Input Frequency	60 Hz	Net Weight (Piece)	0.066 lb
Power Consumption	4 W	Approval and Application	
Lamp Current (Nom)	55 mA	EU RoHS compliant	Yes
Wattage Equivalent	40 W	EyeComfort	Yes
Starting Time (Nom)	0.5 s		

Specialty Lamps

T20 compliant	N/A
LED Innovations	EyeComfort
Ambient temperature range	-4 °F to 113 °F

Application Conditions


can it be used in closed luminaires	No
-------------------------------------	----

Product Data

Order product name	4A19/PER/RED/G/E26/ND 4/1PF
--------------------	-----------------------------


Full product name	4A19/PER/RED/G/E26/ND 4/1PF
Order code	568832
Material Nr. (12NC)	929001937053
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677568832
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677568837

Dimensional drawing




Product	D	C
4A19/PER/RED/G/E26/ND 4/1PF	2-3/8 inch	4-3/16 inch

Photometric data




Light Distribution Diagram - 4A19/PER/RED/G/E26/ND 4/1PF




General uniform lighting - 4A19/PER/RED/G/E26/ND 4/1PF

Specialty Lamps

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 4A19/PER/RED/G/E26/ND 4/1PF

