




Specialty Lamps

4A19/PER/ORANGE/G/E26/ND 4/1PF

LEDbulb, A19, 40 W, E26, 15000 hour(s), Glass

LEDbulb, A19, 40 W, E26, 15000 hour(s), Glass

Product data

General Information	
Cap-Base	E26
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LEDbulb
Light Technical	
Color Code	Orange
Beam Angle (Nom)	330 degree(s)
Color Designation	Orange
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	4 W
Lamp Current (Nom)	55 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.40


Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	257 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Orange
Bulb Material	Glass
Overall length	4-3/16 inch
Overall width	2-3/8 inch
Overall height	4-3/16 inch
Dimensions (Height x Width x Depth)	106 x 60 x 106 mm
Bulb Shape	A19
UL Wet/ damp/ dry location	Wet location
Net Weight (Piece)	0.066 lb
Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes
T20 compliant	N/A

Specialty Lamps

LED Innovations	EyeComfort
Ambient temperature range	-4 °F to 113 °F
Application Conditions	
can it be used in closed luminaires	No
Wireless Technology	Not applicable
Product Data	
Order product name	4A19/PER/ORANGE/G/E26/ND 4/1PF



Full product name	4A19/PER/ORANGE/G/E26/ND 4/1PF
Order code	568840
Material Nr. (12NC)	929001937153
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677568849
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677568844

Dimensional drawing



Product	D	C
4A19/PER/ORANGE/G/E26/ND 4/1PF	2-3/8 inch	4-3/16 inch

Photometric data





Light Distribution Diagram - 4A19/PER/ORANGE/G/E26/ND 4/1PF

General uniform lighting - 4A19/PER/ORANGE/G/E26/ND 4/1PF

Specialty Lamps

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - 4A19/PER/ORANGE/G/E26/ND 4/1PF

