



Specialty Lamps

4A19/PER/BLEUE/G/E26/ND 4/1PF

Philips A shape party lamp provides a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays. Philips Dusk to Dawn A19 lamp is equipped with a built-in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises. Philips 3-Way A shape lamps provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
Light Technical	
Color Code	Blue
Beam Angle (Nom)	330 degree(s)
Color Designation	Blue
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	4 W
Lamp Current (Nom)	55 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s


Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.40
Voltage (Nom)	120 V
Temperature	
Ambient temperature range	-4 °F to 113 °F
T-Case Maximum (Nom)	257 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Blue
Bulb Material	Glass
Bulb Shape	A19
UL Wet/ damp/ dry location	Wet location
Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes

Specialty Lamps

T20 compliant	N/A
LED Innovations	EyeComfort
Application Conditions	
can it be used in closed luminaires	No
Product Data	
Order product name	4A19/PER/BUE/G/E26/ND 4/1PF
Full product name	4A19/PER/BUE/G/E26/ND 4/1PF


Order code	568865
Material Nr. (12NC)	929001937353
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.066 lb
EAN/UPC - Product/Case	046677568863
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677568868

Dimensional drawing



Product	D	C
4A19/PER/BUE/G/E26/ND 4/1PF	2-3/8 inch	4-3/16 inch

Photometric data



OSRAM PHOTOMETRIC DATA | Philips Lighting NV | Page 10

Light Distribution Diagram - 4A19/PER/BUE/G/E26/ND 4/1PF

General uniform lighting - 4A19/PER/BUE/G/E26/ND 4/1PF

Specialty Lamps

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - 4A19/PER/BLUE/G/E26/ND 4/1PF

