



Specialty Lamps

4A19/PER/BUE/G/E26/ND 4/1PF

Philips A shape party lamp provides a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays. Philips Dusk to Dawn A19 lamp is equipped with a built-in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises. Philips 3-Way A shape lamps provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

Product data

General Information			
Cap-Base	E26 [Single Contact Medium Screw]	Starting Time (Nom)	0.5 s
Nominal lifetime	15,000 hour(s)	Warm-up time to 60% light	0.5 s
Switching Cycle	20,000	Power Factor (Fraction)	0.40
Rated Lifetime (Hours)	15,000 hour(s)	Voltage (Nom)	120 V
Lighting Technology	LED	Temperature	
EU RoHS compliant	Yes	Ambient temperature range	-4 °F to 113 °F
Light Technical		T-Case Maximum (Nom)	257 °F
Color Code	Blue	Controls and Dimming	
Beam Angle (Nom)	330 degree(s)	Dimmable	No
Color Designation	Blue	Mechanical and Housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Finish	Blue
Operating and Electrical		Bulb Material	Glass
Line Frequency	60 Hz	Bulb Shape	A19
Input Frequency	60 Hz	UL Wet/ damp/ dry location	Wet location
Power Consumption	4 W	Approval and Application	
Lamp Current (Nom)	55 mA	EyeComfort	Yes
Wattage Equivalent	40 W		

Specialty Lamps

T20 compliant	N/A
LED Innovations	EyeComfort

Application Conditions


can it be used in closed luminaires	No
-------------------------------------	----

Product Data

Order product name	4A19/PER/BLUE/G/E26/ND 4/1PF
Full product name	4A19/PER/BLUE/G/E26/ND 4/1PF


Order code	568865
Material Nr. (12NC)	929001937353
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677568863
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677568868

Dimensional drawing



Product	D	C
4A19/PER/BLUE/G/E26/ND 4/1PF	2-3/8 inch	4-3/16 inch

Photometric data



Light Distribution Diagram - 4A19/PER/BLUE/G/E26/ND 4/1PF

General uniform lighting - 4A19/PER/BLUE/G/E26/ND 4/1PF

Specialty Lamps

Lifetime



Life Expectancy Diagram - 4A19/PER/BLUE/G/E26/ND 4/1PF



Lumen Maintenance Diagram - 4A19/PER/BLUE/G/E26/ND 4/1PF

