

A-Shape LED

4.5A19/VIN/820/E26/CL/GL/DIM 4/FBH T20

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Product data


General Information		Starting Time (Nom)		0.5 s
Cap-Base	E26 [Single Contact Medium Screw]	Warm-up time to 60% light		0.5 s
Nominal lifetime	15,000 hour(s)	Power Factor (Fraction)		0.7
Switching Cycle	20,000	Voltage (Nom)		120 V
Rated Lifetime (Hours)	15,000 hour(s)	Temperature		
Lighting Technology	LED	T-Case Maximum (Nom)		131 °F
EU RoHS compliant	Yes	Controls and Dimming		
Light Technical		Dimmable		Yes
Color Code	820 [CCT of 2000K]	Mechanical and Housing		
Luminous Flux	300 lm	Bulb Finish		Amber
Color Designation	Flame	Bulb Material		Glass
Correlated Color Temperature (Nom)	2000 K	Bulb Shape		A19 [A 19mm]
Luminous Efficacy (rated) (Nom)	66.00 lm/W	UL Wet/ damp/ dry location		Wet location
Color Consistency	<6	Approval and Application		
Color rendering index (CRI)	80	Energy Consumption kWh/1000 h		- kWh
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Certifications		No
Operating and Electrical		EyeComfort		Yes
Line Frequency	60 Hz	T20 compliant		N/A
Input Frequency	60 Hz			
Power Consumption	4.5 W			
Lamp Current (Nom)	40 mA			
Wattage Equivalent	60 W			

A-Shape LED

Application Conditions	
can it be used in closed luminaires	No
Product Data	
Order product name	4.5A19/VIN/820/E26/CL/GL/DIM 4/FBH T20
Full product name	4.5A19/VIN/820/E26/CL/GL/DIM 4/FBH T20
Order code	556795



Material Nr. (12NC)	929001950933
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677556792
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677556797

Dimensional drawing




Product	D	C
4.5A19/VIN/820/E26/CL/GL/DIM 4/FBH T20	2-3/8 inch	4-3/16 inch

Photometric data



Spectral Power Distribution Colour - 4.5A19/VIN/820/E26/CL/GL/DIM 4/FBH T20

Light Distribution Diagram - 4.5A19/VIN/820/E26/CL/GL/DIM 4/FBH T20



General uniform lighting - 4.5A19/VIN/820/E26/CL/GL/DIM 4/FBH T20

A-Shape LED

Lifetime



Life Expectancy Diagram - 4.5A19/VIN/820/E26/CL/GL/DIM 4/FBH T20



Lumen Maintenance Diagram - 4.5A19/VIN/820/E26/CL/GL/DIM 4/FBH T20

