

**PHILIPS****Lighting****F** A  
G

# Classic filament LED candles and lusters

## LED classic 40W T25L E14 CL ND RF SRT4

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

### Product data

General Information		Operating and Electrical	
Cap-Base	E14	Input Frequency	50 to 60 Hz
Nominal lifetime	15,000 hour(s)	Power Consumption	4.5 W
Switching Cycle	20,000	Lamp Current (Nom)	45 mA
Lighting Technology	LED	Wattage Equivalent	40 W
Flux measurement reference	Sphere	Starting Time (Nom)	0.5 s
Light Technical		Warm-up time to 60% light	0.5 s
Color Code	827 [CCT of 2700K]	Power Factor (Fraction)	0.51
Color Code	827 [CCT of 2700K]	Voltage (Nom)	220-240 V
Luminous Flux	470 lm	Temperature	
Color Designation	Warm White (WW)	T-Case Maximum (Nom)	57 °C
Correlated Color Temperature (Nom)	2700 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	104 lm/W	Dimmable	No
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	80	Bulb Finish	Clear
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Material	Glass
Photobiological safety according to EN 62471	RG1	Overall length	90 mm

## Classic filament LED candles and lusters

Overall width	25 mm
Overall height	90 mm
Dimensions (Height x Width x Depth)	90 x 25 x 90 mm
Bulb Shape	T25
Net Weight (Piece)	0.012 kg


Approval and Application	
Energy Efficiency Class	F
Energy Consumption kWh/1000 h	5 kWh
EPREL Registration Number	374880
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +45 °C

Application Conditions	
can it be used in closed luminaires	No



Product Data	
Order product name	LED classic 40W T25L E14 CL ND RF SRT4
Full product name	LED classic 40W T25L E14 CL ND RF SRT4
Full product code	871869978335802
Order code	929001956728
Material Nr. (12NC)	929001956728
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699783358
Numerator - Packs per outer box	4
EAN/UPC - Case	8719514386556

### Dimensional drawing



Product	D	C
LED classic 40W T25L E14 CL ND RF SRT4	25 mm	90 mm

### Photometric data




General uniform lighting - LED classic 40W T25L E14 CL ND RF SRT4

Spectral Power Distribution Colour - LED classic 40W T25L E14 CL ND RF SRT4


## Classic filament LED candles and lusters

### Photometric data




Light Distribution Diagram - LED classic 40W T25L E14 CL ND RF SRT4

### Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LED classic 40W T25L E14 CL ND RF SRT4

