




Classic filament LED bulbs

8A19/PER/927-922/CL/G/E26/WGX 1FB T20

LEDbulb, A19, 60 W, E26, 2700 K, 2200 K, 800 lm, 15000 hour(s), Glass

LEDbulb, A19, 60 W, E26, 2700 K, 2200 K, 800 lm, 15000 hour(s), Glass, 100.00 lm/W

Product data

General Information	
Cap-Base	E26
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LEDbulb
Light Technical	
Color Code	927-922 [CCT of 2700K-2200K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	800 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2700 2200 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	8 W
Lamp Current (Nom)	85 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.75
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	140 °F
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear

Classic filament LED bulbs

Bulb Material	Glass
Overall length	4-1/4 inch
Overall width	2-3/8 inch
Overall height	4-1/4 inch
Dimensions (Height x Width x Depth)	108 x 60 x 108 mm
Bulb Shape	A19
UL Wet/ damp/ dry location	Wet location
Net Weight (Piece)	0.066 lb

Approval and Application

EU RoHS compliant	Yes
EyeComfort	Yes
T20 compliant	Yes
LED Innovations	EyeComfort
Ambient temperature range	-4 to +113 °F


Application Conditions

can it be used in closed luminaires	No
Wireless Technology	Not applicable

Product Data


Order product name	8A19/PER/927-922/CL/G/E26/WGX 1FB T20
Full product name	8A19/PER/927-922/CL/G/E26/WGX 1FB T20
Order code	549493
Material Nr. (12NC)	929001969604
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677549497
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677549492

Dimensional drawing




Product	D	C
8A19/PER/927-922/CL/G/E26/WGX 1FB T20	2-3/8 inch	4-1/4 inch

Photometric data




Spectral Power Distribution Colour - 8A19/PER/927-922/CL/G/E26/WGX 1FB T20



General uniform lighting - 8A19/PER/927-922/CL/G/E26/WGX 1FB T20

Classic filament LED bulbs

Photometric data




Light Distribution Diagram - 8A19/PER/927-922/CL/G/E26/WGX 1FB T20

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 8A19/PER/927-922/CL/G/E26/WGX 1FB T20

