



# Specialty Lamps

## 8W (60W) E26 Red Bulb

Philips A shape party lamp provides a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays. Philips Dusk to Dawn A19 lamp is equipped with a built-in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises. Philips 3-Way A shape lamps provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	10,950 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	10,950 hour(s)
Lighting Technology	LED
Light Technical	
Beam Angle (Nom)	120 degree(s)
Color Consistency	-
Color rendering index (CRI)	-
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	8 W
Lamp Current (Nom)	115 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s


Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19
Net Weight (Piece)	0.060 kg
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
EU RoHS compliant	Yes
EyeComfort	Yes

Specialty Lamps

LED Innovations	EyeComfort
Product Data	
Order product name	8W (60W) E26 Red Bulb
Full product name	8W (60W) E26 Red Bulb
Order code	929001997805
Material Nr. (12NC)	929001997805



Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677463274
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677463279

Dimensional drawing




Product	D	C
8W (60W) E26 Red Bulb	60 mm	107 mm

Photometric data



Light Distribution Diagram - 8A19/LED/RED/P/ND 120V 4/1FB

General uniform lighting - 8A19/LED/RED/P/ND 120V 4/1FB




Spectral Power Distribution Colour - 8A19/LED/RED/P/ND 120V 4/1FB

Specialty Lamps

Lifetime



Lumen Maintenance Diagram - 8A19/LED/RED/P/ND 120V 4/1FB



Life Expectancy Diagram

