



Specialty Lamps

8A19/LED/GREEN/P/ND 120V 4/1FB

LEDbulb, A19, 40 W, E26, 10950 hour(s), Plastic

LEDbulb, A19, 40 W, E26, 10950 hour(s), Plastic

Product data

General Information	
Cap-Base	E26
Nominal lifetime	10,950 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	10,950 hour(s)
Lighting Technology	LEDbulb
Light Technical	
Beam Angle (Nom)	160 degree(s)
Color Consistency	-
Color rendering index (CRI)	-
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	8 W
Lamp Current (Nom)	115 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5


Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	176 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Overall length	4-1/4 inch
Overall width	2-3/8 inch
Overall height	4-1/4 inch
Dimensions (Height x Width x Depth)	107 x 60 x 107 mm
Bulb Shape	A19
Net Weight (Piece)	0.132 lb
Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort

Specialty Lamps

Ambient temperature range	-4 to +113 °F
Application Conditions	
Wireless Technology	Not applicable
Product Data	
Order product name	8W (60W) E26 Green Bulb
Full product name	8A19/LED/GREEN/P/ND 120V 4/1FB



Order code	463281
Material Nr. (12NC)	929001997905
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677463281
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677463286

Dimensional drawing




Product	D	C
8W (60W) E26 Green Bulb	2-3/8 inch	4-1/4 inch

Photometric data



General uniform lighting - 8A19/LED/GREEN/P/ND 120V 4/1FB


Light Distribution Diagram - 8A19/LED/GREEN/P/ND 120V 4/1FB




Spectral Power Distribution Colour - 8A19/LED/GREEN/P/ND 120V 4/1FB

Specialty Lamps

Lifetime



Lumen Maintenance Diagram - 8A19/LED/GREEN/P/ND 120V 4/1FB



Life Expectancy Diagram

