



CorePro GLASS LED candles and lustres

CorePro LEDCandle ND6.5-60W B35E14827CLG

Featuring a classic heritage design, these filament LED candles combine the familiar shapes of classic incandescent bulbs with the benefits of long-lasting LED technology. The LED candle bulb is a very easy choice for people who are looking for a retrofit LED replacement, it provides 90% energy savings compared with conventional lamps. CorePro Glass LED bulbs provide excellent quality of light for stairway lighting. The LED candle bulb offers a lifetime of 15,000 hours to reduce maintenance costs.

Product data

General Information	
Cap base	E14
Nominal lifetime	15,000 h
Switching Cycle	20,000
Lighting Technology	LED
Flux measurement reference	Sphere

Light Technical	
Colour Code	827 [CCT of 2700K]
Luminous Flux	806 lm
Colour designation	Warm White (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	124.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Photobiological safety according to EN 62471	RG1

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	6.5 W
Lamp current (nom.)	50 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.55
Voltage (nom.)	220-240 V

Temperature	
T-Case maximum (nom.)	55 °C

Controls and Dimming	
Dimmable	No

CorePro GLASS LED candles and lustres

Mechanical and Housing

Lamp Finish	Clear
Bulb shape	B35
Net Weight (Piece)	0.012 kg

Approval and Application

Energy Efficiency Class	E
Energy consumption kWh/1,000 hours	7 kWh
EPREL Registration Number	1825170
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM)	1
Stroboscopic effect	0.9


Application Conditions

Can it be used in closed luminaires	No
-------------------------------------	----

Product Data


Order product name	CorePro LEDCandle ND6.5-60W B35E14827CLG
Full product name	CorePro LEDCandle ND6.5-60W B35E14827CLG
Full EOC	871951434746500
Order code	34746500
Material no. (12 NC)	929002028092
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514347465
Numerator – packs per outer box	10
EAN/UPC - Case	8719514347472

Dimensional drawing




Product	D	C
CorePro LEDCandle ND6.5-60W B35E14827CLG	35 mm	97 mm

Photometric data




Light Distribution Diagram - CorePro LEDCandle ND6.5-60W B35E14827CLG



Spectral Power Distribution Colour - CorePro LEDCandle ND6.5-60W B35E14827CLG

CorePro GLASS LED candles and lustres


Photometric data




General uniform lighting - CorePro LEDCandle ND6.5-60W B35E14827CLG

General uniform lighting - CorePro LEDCandle ND6.5-60W B35E14827CLG

Lifetime



Lumen Maintenance Diagram - CorePro LEDCandle ND6.5-60W B35E14827CLG



Life Expectancy Diagram

