



CorePro GLASS LED candles and lustres



CorePro LEDLusterND6.5-60W P45 E14827FRG

CorePro, LEDbulb, P45, 60 W, E14, 2700 K, 806 lm, CRI 80, 15000 h, Glass

Featuring a classic heritage design, these filament LED candles combine the familiar shapes of classic incandescent bulbs with the benefits of long-lasting LED technology. The LED candle bulb is a very easy choice for people who are looking for a retrofit LED replacement, it provides 90% energy savings compared with conventional lamps. CorePro Glass LED bulbs provide excellent quality of light for stairway lighting. The LED candle bulb offers a lifetime of 15,000 hours to reduce maintenance costs.

Product data

General Information	
Cap base	E14
Nominal lifetime	15,000 h
Switching Cycle	20,000
Lighting Technology	LEDbulb
Flux measurement reference	Sphere
Warranty period	2 years

Light Technical	
Colour Code	827 [CCT of 2700K]
Beam angle (nom.)	300 degree(s)
Luminous Flux	806 lm
Colour designation	Warm White (WW)
Correlated Colour Temperature (Nom)	2700 K

Luminous efficacy (rated) (nom.)	124.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Photobiological safety according to EN 62471	RG1


Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	6.5 W
Lamp current (nom.)	50 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s

CorePro GLASS LED candles and lustres

Power Factor (Fraction)	0.55
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Frosted
Bulb material	Glass
Bulb shape	P45
Net Weight (Piece)	0.014 kg
Approval and Application	
Energy Efficiency Class	E
Energy consumption kWh/1,000 hours	7 kWh
EPREL Registration Number	1825183
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes

Flickering value (PstLM)	1
Stroboscopic effect	0.4
Ambient temperature range	-20 to +45 °C
Application Conditions	
Can it be used in closed luminaires	No
Wireless Technology	Not applicable
Product Data	
Order product name	CorePro LEDLusterND6.5-60W P45 E14827FRG
Full product name	CorePro LEDLusterND6.5-60W P45 E14827FRG
Full EOC	871951434760100
Order code	929002028792
Material no. (12 NC)	929002028792
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514347601
Numerator – packs per outer box	10
EAN/UPC - Case	8719514347618


Dimensional drawing




Product	D	C
CorePro LEDLusterND6.5-60W P45 E14827FRG	45 mm	80 mm

CorePro GLASS LED candles and lustres


Photometric data



General uniform lighting - CorePro LEDLusterND6.5-60W P45 E14827FRG




Spectral Power Distribution Colour - CorePro LEDLusterND6.5-60W P45 E14827FRG




Light Distribution Diagram - CorePro LEDLusterND6.5-60W P45 E14827FRG

Lifetime



Lumen Maintenance Diagram - CorePro LEDLusterND6.5-60W P45 E14827FRG



Life Expectancy Diagram

CorePro GLASS LED candles and lustres

