



LED BR30

7.2BR30/COR/940/P/E26/DIM 6/1FB T20

CorePro, LEDbulb, BR30, 65 W, E26, 4000 K, 650 lm, 15000 hour(s), Plastic

CorePro, LEDbulb, BR30, 65 W, E26, 4000 K, 650 lm, 15000 hour(s), Plastic, 90.00 lm/W

Product data

General Information	
Cap-Base	E26
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb
Light Technical	
Color Code	940 [CCT of 4000K]
Beam Angle (Nom)	110 degree(s)
Luminous Flux	650 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	7.2 W

Lamp Current (Nom)	82 mA
Wattage Equivalent	65 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	167 °F
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	BR30
UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.121 lb

LED BR30

Approval and Application

EU RoHS compliant	Yes
T20 compliant	Yes
Ambient temperature range	-4 to +113 °F


Application Conditions

can it be used in closed luminaires	Yes
Wireless Technology	Not applicable


Product Data

Order product name	7.2BR30/COR/940/P/E26/DIM 6/1FB T20
--------------------	-------------------------------------

Dimensional drawing




Photometric data



Light Distribution Diagram - 7.2BR30/COR/940/P/E26/DIM 6/1FB T20

Full product name	7.2BR30/COR/940/P/E26/DIM 6/1FB T20
Order code	545913
Material Nr. (12NC)	929002032204
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677545918
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677545913

Product	D	C
7.2BR30/COR/940/P/E26/DIM 6/1FB T20	3-3/4 inch	5-1/4 inch




CakulaX Photometrics 4.5 Philip Leifring B.V. Page 6

Accent Lighting Spots - 7.2BR30/COR/940/P/E26/DIM 6/1FB T20


LED BR30

Photometric data




Spectral Power Distribution Colour - 7.2BR30/COR/940/P/E26/DIM 6/1FB T20

Lifetime



Lumen Maintenance Diagram - 7.2BR30/COR/940/P/E26/DIM 6/1FB T20



LEDBulbs BR30 120V 19-120W 1200lm 2700K E26 D

