



CorePro Plastic (Dimmable) A-Shape Lamps

8.8A19/COR/940/FR/P/E26/DIM/T20 6/1CT

Dimmable A-shape lamps that offer over 25,000 hours lifetime. Title 20 listed lamps that can be sold in California and ideal for commercial spaces nationwide.

Product data


General Information		Power Consumption	
Cap-Base	E26		8.8 W
Nominal lifetime	25,000 hour(s)	Lamp Current (Nom)	80 mA
Switching Cycle	50,000	Wattage Equivalent	60 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
Light Technical		Warm-up time to 60% light	0.5 s
Color Code	940 [CCT of 4000K]	Power Factor (Fraction)	0.7
Beam Angle (Nom)	200 degree(s)	Voltage (Nom)	120 V
Luminous Flux	800 lm	Temperature	
Color Designation	Cool White (CW)	T-Case Maximum (Nom)	75 °C
Correlated Color Temperature (Nom)	4000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	90 lm/W	Dimmable	Only with specific dimmers
Color Consistency	<4	Mechanical and Housing	
Color rendering index (CRI)	90	Bulb Finish	Frosted
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Material	Plastic
Operating and Electrical		Bulb Shape	A19
Line Frequency	60 Hz	UL Wet/ damp/ dry location	Damp location
Input Frequency	60 Hz		

CorePro Plastic (Dimmable) A-Shape Lamps

Net Weight (Piece)	0.060 kg
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
EU RoHS compliant	Yes
T20 compliant	Yes
Ambient temperature range	-20 to +45 °C
Application Conditions	
can it be used in closed luminaires	No


Product Data	
Order product name	8.8A19/COR/940/FR/P/E26/DIM/T20 6/1CT
Full product name	8.8A19/COR/940/FR/P/E26/DIM/T20 6/1CT
Order code	929002032304
Material Nr. (12NC)	929002032304
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677545895
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677545890

Dimensional drawing




Product	D	C
8.8A19/COR/940/FR/P/E26/DIM/T20 6/1CT	62.5 mm	111.5 mm

Photometric data




Light Distribution Diagram - 8.8A19/COR/940/FR/P/E26/DIM/T20 6/1CT



General uniform lighting - 8.8A19/COR/940/FR/P/E26/DIM/T20 6/1CT


CorePro Plastic (Dimmable) A-Shape Lamps

Photometric data




Spectral Power Distribution Colour - 8.8A19/COR/940/FR/P/E26/DIM/T20 6/1CT

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 8.8A19/COR/940/FR/P/E26/DIM/T20 6/1CT

