



# CorePro Plastic (Dimmable) A-Shape Lamps

5A19/COR/927/FR/P/E26/DIM/T20 6/1CT

Dimmable A-shape lamps that offer over 25,000 hours lifetime. Title 20 listed lamps that can be sold in California and ideal for commercial spaces nationwide.

## Product data

General Information	
Cap-Base	E26
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Light Technical	
Color Code	927 [CCT of 2700K]
Beam Angle (Nom)	200 degree(s)
Luminous Flux	450 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz

Power Consumption	5 W
Lamp Current (Nom)	55 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	65 °C

Controls and Dimming	
Dimmable	Only with specific dimmers


Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19
UL Wet/ damp/ dry location	Damp location

# CorePro Plastic (Dimmable) A-Shape Lamps

Net Weight (Piece)	0.060 kg
<b>Approval and Application</b>	
Energy Consumption kWh/1000 h	- kWh
EU RoHS compliant	Yes
T20 compliant	Yes
Ambient temperature range	-20 to +45 °C
<b>Application Conditions</b>	
can it be used in closed luminaires	No


<b>Product Data</b>	
Order product name	5A19/COR/927/FR/P/E26/DIM/T20 6/1CT
Full product name	5A19/COR/927/FR/P/E26/DIM/T20 6/1CT
Order code	929002035704
Material Nr. (12NC)	929002035704
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677550400
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677550405

## Dimensional drawing




Product	D	C
5A19/COR/927/FR/P/E26/DIM/T20 6/1CT	62.5 mm	111.5 mm

## Photometric data




Spectral Power Distribution Colour - 5A19/COR/927/FR/P/E26/DIM/T20 6/1CT



Light Distribution Diagram - 5A19/COR/927/FR/P/E26/DIM/T20 6/1CT

# CorePro Plastic (Dimmable) A-Shape Lamps


## Photometric data




General uniform lighting - 5A19/COR/927/FR/P/E26/DIM/T20 6/1CT

General uniform lighting - 5A19/COR/927/FR/P/E26/DIM/T20 6/1CT

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 5A19/COR/927/FR/P/E26/DIM/T20 6/1CT

