



# CorePro Plastic (Dimmable) A-Shape Lamps

## 5A19/PER/930/P/E26/DIM 6/1FB T20

Dimmable A-shape lamps that offer over 25,000 hours lifetime. Title 20 listed lamps that can be sold in California and ideal for commercial spaces nationwide.

### Product data


General Information			
Cap-Base	E26 [Single Contact Medium Screw]	Power Consumption	5 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	55 mA
Switching Cycle	50,000	Wattage Equivalent	40 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
		Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.7
		Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	930 [CCT of 3000K]	T-Case Maximum (Nom)	75 °C
Beam Angle (Nom)	250 degree(s)		
Luminous Flux	450 lm	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Dimmable	Yes
Color Designation	White (WH)		
Correlated Color Temperature (Nom)	3000 K	Mechanical and Housing	
Color Consistency	<4	Bulb Finish	Frosted
Color rendering index (CRI)	90	Bulb Material	Plastic
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	A19
Operating and Electrical			
Line Frequency	60 Hz		
Input Frequency	60 Hz		

CorePro Plastic (Dimmable) A-Shape Lamps

Approval and Application	
Energy Consumption kWh/1000 h	- kWh
EU RoHS compliant	Yes
Product Data	
Order product name	5A19/PER/930/P/E26/DIM 6/1FB T20
Full product name	5A19/PER/930/P/E26/DIM 6/1FB T20
Order code	929002035804


Material Nr. (12NC)	929002035804
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.060 kg
EAN/UPC - Product/Case	046677550417
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677550412

Dimensional drawing




Product	D	C
5A19/PER/930/P/E26/DIM 6/1FB T20	62.5 mm	111.5 mm


Photometric data



Spectral Power Distribution Colour - 5A19/PER/930/P/E26/DIM 6/1FB T20



Light Distribution Diagram - 5A19/PER/930/P/E26/DIM 6/1FB T20



General uniform lighting - 5A19/PER/930/P/E26/DIM 6/1FB T20

General uniform lighting - 5A19/PER/930/P/E26/DIM 6/1FB T20

CorePro Plastic (Dimmable) A-Shape Lamps

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 5A19/PER/930/P/E26/DIM 6/1FB T20

