



# CorePro Plastic (Dimmable) A-Shape Lamps

## 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT

Dimmable A-shape lamps that offer over 25,000 hours lifetime. Title 20 listed lamps that can be sold in California and ideal for commercial spaces nationwide.

### Product data


<b>General Information</b>		<b>Power Consumption</b>	
Cap-Base	E26		8.8 W
Nominal lifetime	25,000 hour(s)	Lamp Current (Nom)	80 mA
Switching Cycle	50,000	Wattage Equivalent	60 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
		Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.7
		Voltage (Nom)	120 V
<b>Light Technical</b>		<b>Temperature</b>	
Color Code	930 [CCT of 3000K]		
Beam Angle (Nom)	200 degree(s)	T-Case Maximum (Nom)	75 °C
Luminous Flux	800 lm		
Color Designation	White (WH)	<b>Controls and Dimming</b>	
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	90 lm/W	Dimmable	Only with specific dimmers
Color Consistency	<4		
Color rendering index (CRI)	90	<b>Mechanical and Housing</b>	
LLMF At End Of Nominal Lifetime (Nom)	70 %		
		Bulb Finish	Frosted
<b>Operating and Electrical</b>		Bulb Material	Plastic
Line Frequency	60 Hz	Bulb Shape	A19
Input Frequency	60 Hz	UL Wet/ damp/ dry location	Damp location

## CorePro Plastic (Dimmable) A-Shape Lamps

Net Weight (Piece)	0.060 kg
<b>Approval and Application</b>	
Energy Consumption kWh/1000 h	- kWh
EU RoHS compliant	Yes
T20 compliant	Yes
Ambient temperature range	-20 to +45 °C
<b>Application Conditions</b>	
can it be used in closed luminaires	No


Product Data	
Order product name	8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT
Full product name	8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT
Order code	929002036204
Material Nr. (12NC)	929002036204
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677550448
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677550443

## Dimensional drawing




Product	D	C
8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT	62.5 mm	111.5 mm

## Photometric data




**Light Distribution Diagram - 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT**



General uniform lighting - 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT


# CorePro Plastic (Dimmable) A-Shape Lamps

## Photometric data




Spectral Power Distribution Colour - 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT

