



LED PAR30 S/L

9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	25 degree(s)
Luminous Flux	850 lm
Luminous Intensity (Nom)	2,910 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	9.4 W
Lamp Current (Nom)	90 mA
Wattage Equivalent	75 W


Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	PAR30S
Net Weight (Piece)	0.134 kg
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
EU RoHS compliant	Yes

LED PAR30 S/L

Product Data	
Order product name	9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB
Full product name	9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB
Order code	929002045604
Material Nr. (12NC)	929002045604


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677546984
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677546989

Dimensional drawing




Product	D	C
9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB	97 mm	94 mm


Photometric data



Light Distribution Diagram - 9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB



Spectral Power Distribution Colour - 9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB



Accent Lighting Spots - 9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB


Accent Lighting Spots - 9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB

LED PAR30 S/L

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB

