

LED BA11

5.5F15/PER/927-922/CL/G/E26/WGX 1PF T20

LEDbulb, F15, 60 W, E26, 2200 K, 2700 K, 500 lm, 15000 hour(s), Glass

LEDbulb, F15, 60 W, E26, 2200 K, 2700 K, 500 lm, 15000 hour(s), Glass, 90 lm/W

Product data

General Information		Wattage Equivalent	
Cap-Base	E26	60 W	
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)	
Switching Cycle	20,000	0.5 s	
Lighting Technology	LEDbulb	Warm-up time to 60% light	
		0.5 s	
		Power Factor (Fraction)	
		0.75	
		Voltage (Nom)	
		120 V	
Light Technical		Temperature	
Color Code	922-927 [CCT of 2200K-2700K]	T-Case Maximum (Nom)	
Beam Angle (Nom)	300 degree(s)	140 °F	
Luminous Flux	500 lm		
Color Designation	Warm Glow(WG)	Controls and Dimming	
Correlated Color Temperature (Nom)	2200 2700 K	Dimmable	
Luminous Efficacy (rated) (Nom)	90 lm/W	Only with specific dimmers	
Color Consistency	<4		
Color rendering index (CRI)	90		
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical		Mechanical and Housing	
Line Frequency	50 to 60 Hz	Bulb Finish	
Input Frequency	50 to 60 Hz	Clear	
Power Consumption	5.5 W	Bulb Material	
Lamp Current (Nom)	60 mA	Glass	
		Bulb Shape	
		F15	
		UL Wet/ damp/ dry location	
		Wet location	
		Net Weight (Piece)	
		0.055 lb	
		Approval and Application	
		EU RoHS compliant	
		Yes	
		T20 compliant	
		Yes	

LED BA11

Ambient temperature range	-4 °F to 113 °F
---------------------------	-----------------

Application Conditions


can it be used in closed luminaires	No
Wireless Technology	Not applicable

Product Data

Order product name	5.5F15/PER/927-922/CL/G/E26/WGX 1PF T20
Full product name	5.5F15/PER/927-922/CL/G/E26/WGX 1PF T20


Order code	572669
Material Nr. (12NC)	929002091593
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677572662
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677572667

Dimensional drawing




Product	D	C
5.5F15/PER/927-922/CL/G/E26/WGX 1PF T20	1-7/8 inch	4-7/16 inch


Photometric data



Spectral Power Distribution Colour - 5.5F15/PER/927-922/CL/G/E26/WGX
1PF T20



General uniform lighting - 5.5F15/PER/927-922/CL/G/E26/WGX 1PF T20



Light Distribution Diagram - 5.5F15/PER/927-922/CL/G/E26/WGX 1PF T20

LED BA11

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 5.5F15/PER/927-922/CL/G/E26/WGX 1PF T20

