



LED A15

5.5A15/PER/927-922/CL/G/E26/WGX1FB

Philips A15 LED Lamps offer energy saving ambience with an elegant effect. Their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED

Light Technical	
Color Code	927-922 [CCT of 2700K-2200K]
Luminous Flux	500 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2700 2200 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	5.5 W
Lamp Current (Nom)	60 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s

Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.75
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	60 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	A15
UL Wet/ damp/ dry location	Wet location
Net Weight (Piece)	0.020 kg


Approval and Application	
Energy Consumption kWh/1000 h	- kWh
EU RoHS compliant	Yes
EyeComfort	Yes
T20 compliant	No
LED Innovations	EyeComfort

LED A15

Application Conditions	
can it be used in closed luminaires	No
Product Data	
Order product name	5.5A15/PER/927-922/CL/G/E26/WGX1FB
Full product name	5.5A15/PER/927-922/CL/G/E26/WGX1FB
Order code	929002208604


Material Nr. (12NC)	929002208604
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677549404
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677549409

Dimensional drawing




Product	D	C
5.5A15/PER/927-922/CL/G/E26/WGX1FB	47 mm	86 mm


Photometric data



Spectral Power Distribution Colour - 5.5A15/PER/927-922/CL/G/E26/WGX1FB




Light Distribution Diagram - 5.5A15/PER/927-922/CL/G/E26/WGX1FB




General uniform lighting - 5.5A15/PER/927-922/CL/G/E26/WGX1FB

LED A15

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 5.5A15/PER/927-922/CL/G/E26/WGX1FB

