



LED AR111

12AR111/LED/930/S8/DIM/EC 12V 6/1FB

LEDspot, AR111, 50 W, G53, 3000 K, 680 lm, 40000 hour(s), Plastic

LEDspot, AR111, 50 W, G53, 3000 K, 680 lm, 40000 hour(s), Plastic, 56.00 lm/W

Product data

General Information	
Cap-Base	G53
Nominal lifetime	40,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	8 degree(s)
Luminous Flux	680 lm
Luminous Intensity (Nom)	8,000 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	56.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	97
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	- Hz
Input Frequency	- Hz
Power Consumption	12 W


Lamp Current (Nom)	1,300 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	ac electronic 12 V
Temperature	
T-Case Maximum (Nom)	158 °F
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	AR111
UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.353 lb
Approval and Application	
Suitable For Accent Lighting	Yes

LED AR111

Energy Certifications	No
EU RoHS compliant	Yes
T20 compliant	N/A
Ambient temperature range	-4 to +113 °F
Application Conditions	
can it be used in closed luminaires	No
Wireless Technology	Not applicable
Product Data	
Order product name	12AR111/LED/930/S8/DIM/EC 12V 6/1FB



Full product name	12AR111/LED/930/S8/DIM/EC 12V 6/1FB
Order code	552406
Material Nr. (12NC)	929002238504
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677552404
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677552409

Dimensional drawing



Product	D	C
12AR111/LED/930/S8/DIM/EC 12V 6/1FB	4-3/8 inch	2-1/2 inch

Photometric data




Spectral Power Distribution Colour - 12AR111/LED/930/S8/DIM/EC 12V 6/1FB

General uniform lighting - 12AR111/LED/930/S8/DIM/EC 12V 6/1FB


LED AR111

Photometric data




Light Distribution Diagram - 12AR111/LED/930/S8/DIM/EC 12V 6/1FB

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 12AR111/LED/930/S8/DIM/EC 12V 6/1FB

