



MasterClass Plastic (WarmGlow) A-Shape Lamps

12.2A19/MAS/927-22/FR/P/E26/T20 6/1CT

MasterClass, LEDbulb, A19, 75 W, E26, 2200 K, 2700 K, 1100 lm, 25000 hour(s), Plastic

MasterClass, LEDbulb, A19, 75 W, E26, 2200 K, 2700 K, 1100 lm, 25000 hour(s), Plastic, 90 lm/W

Product data

General Information	
Cap-Base	E26
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb
Light Technical	
Color Code	922-927 [CCT of 2200K-2700K]
Beam Angle (Nom)	200 degree(s)
Luminous Flux	1,100 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2200 2700 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color Consistency	<4
Color rendering index (CRI)	90


LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	12.2 W
Lamp Current (Nom)	120 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	194 °F

MasterClass Plastic (WarmGlow) A-Shape Lamps

Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19
UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.132 lb
Approval and Application	
EU RoHS compliant	Yes
T20 compliant	Yes
Ambient temperature range	-4 to +113 °F


Application Conditions	
can it be used in closed luminaires	No
Wireless Technology	Not applicable
Product Data	
Order product name	12.2A19/MAS/927-22/FR/P/E26/T20 6/1CT
Full product name	12.2A19/MAS/927-22/FR/P/E26/T20 6/1CT
Order code	561000
Material Nr. (12NC)	929002285404
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677561000
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677561005

Dimensional drawing




Product	D	C
12.2A19/MAS/927-22/FR/P/E26/T20 6/1CT	2-3/8 inch	4-7/16 inch

Photometric data




Light Distribution Diagram - 12.2A19/MAS/927-22/FR/P/E26/T20 6/1CT



Spectral Power Distribution Colour - 12.2A19/MAS/927-22/FR/P/E26/T20 6/1CT

MasterClass Plastic (WarmGlow) A-Shape Lamps



Photometric data



Calcutt, Photomicros 4.5 Polys Lighting B.V. Page: 1/1

General uniform lighting - 12.2A19/MAS/927-22/FR/P/E26/T20 6/1CT

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - 12.2A19/MAS/927-22/FR/P/E26/T20 6/1CT

