



CorePro Plastic (Dimmable) A-Shape Lamps

8.8A19/PER/930/P/GU24/DIM 6/1FB T20

Dimmable A-shape lamps that offer over 25,000 hours lifetime. Title 20 listed lamps that can be sold in California and ideal for commercial spaces nationwide.

Product data


General Information		Operating and Electrical	
Cap-Base	GU24	Line Frequency	60 Hz
Nominal lifetime	15,000 hour(s)	Input Frequency	60 Hz
Switching Cycle	50,000	Power Consumption	8.8 W
Rated Lifetime (Hours)	15,000 hour(s)	Lamp Current (Nom)	80 mA
Lighting Technology	LED	Wattage Equivalent	60 W
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
		Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.7
		Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	930 [CCT of 3000K]	T-Case Maximum (Nom)	90 °C
Color Code	930 [CCT of 3000K]		
Beam Angle (Nom)	250 degree(s)		
Luminous Flux	800 lm		
Color Designation	White (WH)		
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	90.00 lm/W		
Color Consistency	<4		
Color rendering index (CRI)	90		
LLMF At End Of Nominal Lifetime (Nom)	70 %		
		Controls and Dimming	
		Dimmable	Yes
		Mechanical and Housing	
		Bulb Finish	Frosted
		Bulb Material	Plastic

CorePro Plastic (Dimmable) A-Shape Lamps

Bulb Shape	A19 [A 19mm]
UL Wet/ damp/ dry location	Damp location
Approval and Application	
Energy Certifications	Energy Star
EyeComfort	Yes
T20 compliant	Yes
Application Conditions	
can it be used in closed luminaires	Yes



Product Data	
Order product name	8.8A19/PER/930/P/GU24/DIM 6/1FB T20
Full product name	8.8A19/PER/930/P/GU24/DIM 6/1FB T20
Order code	557660
Material Nr. (12NC)	929002327504
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677557669
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677557664

Dimensional drawing



Product	D	C
8.8A19/PER/930/P/GU24/DIM 6/1FB T20	60 mm	106 mm

Photometric data




General uniform lighting - 8.8A19/PER/930/P/GU24/DIM 6/1FB T20

Light Distribution Diagram - 8.8A19/PER/930/P/GU24/DIM 6/1FB T20


CorePro Plastic (Dimmable) A-Shape Lamps

Photometric data




Spectral Power Distribution Colour - 8.8A19/PER/930/P/GU24/DIM 6/1FB T20

Lifetime



Life Expectancy Diagram - 8.8A19/PER/930/P/GU24/DIM 6/1FB T20



Lumen Maintenance Diagram - 8.8A19/PER/930/P/GU24/DIM 6/1FB T20

