



CorePro Plastic (Dimmable) A-Shape Lamps

8.8A19/PER/930/P/GU24/DIM 6/1FB T20

Dimmable A-shape lamps that offer over 25,000 hours lifetime. Title 20 listed lamps that can be sold in California and ideal for commercial spaces nationwide.

Product data


General Information		Operating and Electrical	
Cap-Base	GU24	Line Frequency	60 Hz
Nominal lifetime	15,000 hour(s)	Input Frequency	60 Hz
Switching Cycle	50,000	Power Consumption	8.8 W
Rated Lifetime (Hours)	15,000 hour(s)	Lamp Current (Nom)	80 mA
Lighting Technology	LED	Wattage Equivalent	60 W
Light Technical		Starting Time (Nom)	0.5 s
Color Code	930 [CCT of 3000K]	Warm-up time to 60% light	0.5 s
Color Code	930 [CCT of 3000K]	Power Factor (Fraction)	0.7
Beam Angle (Nom)	250 degree(s)	Voltage (Nom)	120 V
Luminous Flux	800 lm	Temperature	
Color Designation	White (WH)	T-Case Maximum (Nom)	194 °F
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Controls and Dimming	
Correlated Color Temperature (Nom)	3000 K	Dimmable	Yes
Color Consistency	<4	Mechanical and Housing	
Color rendering index (CRI)	90	Bulb Finish	Frosted
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Material	Plastic

CorePro Plastic (Dimmable) A-Shape Lamps

Bulb Shape	A19
UL Wet/ damp/ dry location	Damp location
Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes
T20 compliant	Yes
LED Innovations	EyeComfort
Application Conditions	
can it be used in closed luminaires	Yes



Product Data	
Order product name	8.8A19/PER/930/P/GU24/DIM 6/1FB T20
Full product name	8.8A19/PER/930/P/GU24/DIM 6/1FB T20
Order code	557660
Material Nr. (12NC)	929002327504
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.132 lb
EAN/UPC - Product/Case	046677557669
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677557664

Dimensional drawing



Product	D	C
8.8A19/PER/930/P/GU24/DIM 6/1FB T20	2-3/8 inch	4-3/16 inch

Photometric data




General uniform lighting - 8.8A19/PER/930/P/GU24/DIM 6/1FB T20

Light Distribution Diagram - 8.8A19/PER/930/P/GU24/DIM 6/1FB T20


CorePro Plastic (Dimmable) A-Shape Lamps

Photometric data




Spectral Power Distribution Colour - 8.8A19/PER/930/P/GU24/DIM 6/1FB T20

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 8.8A19/PER/930/P/GU24/DIM 6/1FB T20

