



# Specialty Lamps

## 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF

Philips A shape party lamp provides a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays. Philips Dusk to Dawn A19 lamp is equipped with a built-in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises. Philips 3-Way A shape lamps provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
Light Technical	
Color Code	927 [CCT of 2700K]
Color Code	927 [CCT of 2700K]
Beam Angle (Nom)	220 degree(s)
Luminous Flux	800 lm
Color Designation	Warm White (WW)
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Correlated Color Temperature (Nom)	2700 K
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	8.8 W
Lamp Current (Nom)	74 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	203 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A19

# Specialty Lamps

UL Wet/ damp/ dry location	Damp location
----------------------------	---------------

## Approval and Application

EU RoHS compliant	Yes
EyeComfort	Yes
T20 compliant	Yes
LED Innovations	EyeComfort

## Application Conditions


can it be used in closed luminaires	Yes
-------------------------------------	-----

## Product Data

Order product name	8.8A19/PER/927/FR/P/E26/D2D/T20 4/IPF
--------------------	---------------------------------------



Full product name	8.8A19/PER/927/FR/P/E26/D2D/T20 4/IPF
Order code	573238
Material Nr. (12NC)	929002333693
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.132 lb
EAN/UPC - Product/Case	046677573232
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677573237

## Dimensional drawing



Product	D	C
8.8A19/PER/927/FR/P/E26/D2D/T20 4/IPF	2-7/16 inch	4-3/8 inch

## Photometric data




General uniform lighting - 8.8A19/PER/927/FR/P/E26/D2D/T20 4/IPF

Spectral Power Distribution Colour - 8.8A19/PER/927/FR/P/E26/D2D/T20 4/IPF

General uniform lighting - 8.8A19/PER/927/FR/P/E26/D2D/T20 4/IPF

# Specialty Lamps

## Photometric data




Light Distribution Diagram - 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF

