



Specialty Lamps

8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF

Philips A shape party lamp provides a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays. Philips Dusk to Dawn A19 lamp is equipped with a built-in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises. Philips 3-Way A shape lamps provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

Product data

| General Information | |
|---------------------------------------|-----------------------------------|
| Cap-Base | E26 [Single Contact Medium Screw] |
| Nominal lifetime | 15,000 hour(s) |
| Switching Cycle | 50,000 |
| Rated Lifetime (Hours) | 15,000 hour(s) |
| Lighting Technology | LED |
| Light Technical | |
| Color Code | 927 [CCT of 2700K] |
| Color Code | 927 [CCT of 2700K] |
| Beam Angle (Nom) | 220 degree(s) |
| Luminous Flux | 800 lm |
| Color Designation | Warm White (WW) |
| Luminous Efficacy (rated) (Nom) | 90.00 lm/W |
| Correlated Color Temperature (Nom) | 2700 K |
| Color Consistency | <4 |
| Color rendering index (CRI) | 90 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |

| Operating and Electrical | |
|---------------------------|-------|
| Line Frequency | 60 Hz |
| Input Frequency | 60 Hz |
| Power Consumption | 8.8 W |
| Lamp Current (Nom) | 74 mA |
| Wattage Equivalent | 60 W |
| Starting Time (Nom) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.7 |
| Voltage (Nom) | 120 V |

| Temperature | |
|----------------------|--------|
| T-Case Maximum (Nom) | 203 °F |

| Controls and Dimming | |
|----------------------|----|
| Dimmable | No |


| Mechanical and Housing | |
|------------------------|---------|
| Bulb Finish | Frosted |
| Bulb Shape | A19 |

Specialty Lamps

| | |
|-------------------------------------|---------------|
| UL Wet/ damp/ dry location | Damp location |
| Approval and Application | |
| EU RoHS compliant | Yes |
| EyeComfort | Yes |
| T20 compliant | Yes |
| LED Innovations | EyeComfort |
| Application Conditions | |
| can it be used in closed luminaires | Yes |



| | |
|---------------------------------|---------------------------------------|
| Product Data | |
| Order product name | 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF |
| Full product name | 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF |
| Order code | 573238 |
| Material Nr. (12NC) | 929002333693 |
| Net Weight (Piece) | 0.132 lb |
| EAN/UPC - Product/Case | 046677573232 |
| Numerator - Packs per outer box | 4 |
| EAN/UPC - Case | 50046677573237 |

Dimensional drawing



| Product | D | C |
|---------------------------------------|-------------|------------|
| 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF | 2-7/16 inch | 4-3/8 inch |

Photometric data




Spectral Power Distribution Colour - 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF

General uniform lighting - 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF

Specialty Lamps

Photometric data




Light Distribution Diagram - 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF

