



Specialty Lamps

8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF

Philips A shape party lamp provides a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays. Philips Dusk to Dawn A19 lamp is equipped with a built-in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises. Philips 3-Way A shape lamps provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

Product data


General Information		Operating and Electrical	
Cap-Base	E26 [Single Contact Medium Screw]	Line Frequency	60 Hz
Nominal lifetime	15,000 hour(s)	Input Frequency	60 Hz
Switching Cycle	50,000	Power Consumption	8.8 W
Rated Lifetime (Hours)	15,000 hour(s)	Lamp Current (Nom)	74 mA
Lighting Technology	LED	Wattage Equivalent	60 W
Light Technical		Starting Time (Nom)	0.5 s
Color Code	927 [CCT of 2700K]	Warm-up time to 60% light	0.5 s
Color Code	927 [CCT of 2700K]	Power Factor (Fraction)	0.7
Beam Angle (Nom)	220 degree(s)	Voltage (Nom)	120 V
Luminous Flux	800 lm	Temperature	
Color Designation	Warm White (WW)	T-Case Maximum (Nom)	203 °F
Correlated Color Temperature (Nom)	2700 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Dimmable	No
Color Consistency	<4	Mechanical and Housing	
Color rendering index (CRI)	90	Bulb Finish	Frosted
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	A19

Specialty Lamps

UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.132 lb
Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes
T20 compliant	Yes
LED Innovations	EyeComfort
Application Conditions	
can it be used in closed luminaires	Yes


Product Data	
Order product name	8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF
Full product name	8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF
Order code	573238
Material Nr. (12NC)	929002333693
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677573232
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677573237

Dimensional drawing




Product	D	C
8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF	2-7/16 inch	4-3/8 inch

Photometric data




Spectral Power Distribution Colour - 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF



General uniform lighting - 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF


Specialty Lamps

Photometric data




Light Distribution Diagram - 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF

