



MASTER LEDtube InstantFit HF T5



Master LEDtube HF 1500mm HO 26W 865 T5 OE

MASTER, LEDtube, T5, HF, 1500 mm, 26 W, 49W TL5 HO, 6500 K, 3900 lm, CRI 80, 60000 h

The Philips MASTER LEDtube integrates an LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance, which cannot be distinguished from traditional fluorescents. These T5 lighting tubes are the right choice for absolute performance and are designed to stand up to everyday conditions. Unparalleled savings, thanks to low energy consumption and an exceptionally long lifetime, make these T5 LED tubes the choice for every demanding applications.

Product data

General Information		Colour consistency	
Cap base	G5	Colour consistency	<6
Nominal lifetime	60,000 h	Colour rendering index (CRI)	80
Switching Cycle	50,000	LLMF at end of nominal lifetime (nom.)	70 %
Lighting Technology	LEDtube	Photobiological safety according to EN 62471	RG0
Flux measurement reference	Sphere	Operating and Electrical	
Light Technical		Line Frequency	20K to 140K Hz
Colour Code	865 [CCT of 6500K]	Input frequency	20 K to 140 K Hz
Beam angle (nom.)	200 degree(s)	Power Consumption	26 W
Luminous Flux	3,900 lm	Lamp current (max.)	420 mA
Colour designation	Cool Daylight	Lamp current (min.)	150 mA
Correlated Colour Temperature (Nom)	6500 K	Starting time (nom.)	0.5 s
Luminous efficacy (rated) (nom.)	150 lm/W	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.92

MASTER LEDtube InstantFit HF T5

Voltage (nom.)	60-120 V
LED alternative to fluorescent lamp power	49W TL5 HO
Inrush current at mains	-
Max. lamp no. on MCB B type 10A – Mains	-
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	-
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	-
Max. lamp no. on MCB B type 16A – Mains	-
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	-
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	-
Ballast Compatibility	HF

Temperature

T-Case maximum (nom.)	50 °C
-----------------------	-------

Controls and Dimming

Dimmable	Yes – Check ballast compatibility
----------	-----------------------------------

Mechanical and Housing

Lamp Finish	Frosted
Bulb material	Glass
Product length	1,500 mm
Bulb shape	T5
Net Weight (Piece)	0.196 kg


Approval and Application

Energy Efficiency Class	D
Energy-saving product	Yes
Approval marks	RoHS compliance KEMA Keur certificate
Energy consumption kWh/1,000 hours	26 kWh
EPREL Registration Number	1384145
CE mark	Yes
EU RoHS compliant	Yes
Ambient temperature range	-20°C to 45°C

Product Data

Order product name	MAS LEDtube HF 1500mm HO 26W 865 T5 OE
Full product name	Master LEDtube HF 1500mm HO 26W 865 T5 OE
Full EOC	871869974961300
Order code	74961300
Material no. (12 NC)	929002352502
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699749613
Numerator – packs per outer box	10
EAN/UPC – Case	8718699749620



Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube HF 1500mm HO 26W 865 T5 OE	15.5 mm	19 mm	1,449 mm	1,456 mm	1,463 mm


MASTER LEDtube InstantFit HF T5

Lifetime



Lumen Maintenance Diagram - MAS LEDtube HF 1500mm HO 26W 865 T5
OE

Life Expectancy Diagram



LEDtube 60K 5070 FailureRate-LED

