



# LEDLamps

## LEDGlobe 7-60W G95 E27 WW 230V\_AU

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

### Product data

| General Information                   |                    |
|---------------------------------------|--------------------|
| Cap-Base                              | E27                |
| Nominal lifetime                      | 15,000 hour(s)     |
| Switching Cycle                       | 50,000             |
| Rated Lifetime (Hours)                | 15,000 hour(s)     |
| Lighting Technology                   | LED                |
| EU RoHS compliant                     | Yes                |
| Light Technical                       |                    |
| Color Code                            | 827 [CCT of 2700K] |
| Color Code                            | 827 [CCT of 2700K] |
| Beam Angle (Nom)                      | 150 degree(s)      |
| Luminous Flux                         | 806 lm             |
| Color Designation                     | Warm White (WW)    |
| Correlated Color Temperature (Nom)    | 2700 K             |
| Luminous Efficacy (rated) (Nom)       | 115 lm/W           |
| Color Consistency                     | <6                 |
| Color rendering index (CRI)           | 80                 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 %               |
| Operating and Electrical              |                    |
| Input Frequency                       | 50 to 60 Hz        |
| Power Consumption                     | 7 W                |


| Lamp Current (Nom)            | 60 mA         |
|-------------------------------|---------------|
| Wattage Equivalent            | 60 W          |
| Starting Time (Nom)           | 0.5 s         |
| Warm-up time to 60% light     | 0.5 s         |
| Power Factor (Fraction)       | 0.7           |
| Voltage (Nom)                 | 220-240 V     |
| Temperature                   |               |
| Ambient temperature range     | -20 to +45 °C |
| T-Case Maximum (Nom)          | 45 °C         |
| Controls and Dimming          |               |
| Dimmable                      | No            |
| Mechanical and Housing        |               |
| Bulb Finish                   | Frosted       |
| Bulb Material                 | Plastic       |
| Bulb Shape                    | G95           |
| Approval and Application      |               |
| Energy Consumption kWh/1000 h | 7 kWh         |
| EyeComfort                    | Yes           |

LEDLamps

|                    |                                   |
|--------------------|-----------------------------------|
| LED Innovations    | EyeComfort                        |
| Product Data       |                                   |
| Order product name | LEDGlobe 7-60W G95 E27 WW 230V_AU |
| Full product name  | LEDGlobe 7-60W G95 E27 WW 230V_AU |
| Full product code  | 871869673246500                   |
| Order code         | 929002441669                      |


|                                 |               |
|---------------------------------|---------------|
| Material Nr. (12NC)             | 929002441669  |
| Numerator - Quantity Per Pack   | 1             |
| EAN/UPC - Product/Case          | 8718696732465 |
| Numerator - Packs per outer box | 3             |
| EAN/UPC - Case                  | 8719514271357 |

Dimensional drawing




| Product                           | D     | C      |
|-----------------------------------|-------|--------|
| LEDGlobe 7-60W G95 E27 WW 230V_AU | 95 mm | 137 mm |


Photometric data



Light Distribution Diagram - LEDGlobe 7-60W G95 E27 WW 230V\_AU



Spectral Power Distribution Colour - LEDGlobe 7-60W G95 E27 WW 230V\_AU



General uniform lighting - LEDGlobe 7-60W G95 E27 WW 230V\_AU

Lifetime



Life Expectancy Diagram - LEDGlobe 7-60W G95 E27 WW 230V\_AU



Lumen Maintenance Diagram - LEDGlobe 7-60W G95 E27 WW 230V\_AU

